

Previously known as: Winter Monkey Grip® 23-193



Cold



Heavy Duty

Cold-resistant, flexible and robust PVC-coated gloves with water, oil and grease resistance

- **Enhanced versatility:** ActivArm® Winter Monkey Grip® 23-193 protective gloves' PVC coating guards against water, oil and grease, while remaining soft and flexible in cold conditions and improving abrasion resistance and grip performance
- **Added comfort:** Thanks to their foam insulation, these comfortable breathable work gloves keep hands warm and dry
- **Improved ergonomics:** In addition, these hand protection gloves feature a uniquely designed wing thumb, along with curved fingers and a soft jersey cotton lining, resulting in greater flexibility and dexterity
- **Certified cold resistance:** As these safety gloves also meet EN 511-111 contact cold standards, they grant reliable hand protection in low temperatures



Industries

- Metal fabrication

Applications

- Handling materials with sharp or rough edges
- Fabricating metal parts, glass sheets
- Handling application & cleaning tools
- Production line support & maintenance
- Equipment repair & maintenance
- Assembly and disassembly of equipment

Previously known as: Winter Monkey Grip® 23-193

Key Features

- **Flexible PVC coating:** Superb grip performance and durability
- **Foam insulation:** For industrial gloves ensuring warm and dry hands
- **Curved fingers, wing thumb and jersey lining:** Increased comfort

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3121B

EN 511



111

Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArmr Winter Monkey Grip® 23-193	Finishing: Fully Coated, Smooth Coating Material: PVC Liner Material: Cotton Jersey Cuff Style: Safety Cuff		10, 11	265-290 mm, 10"-12"	Orange	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699