

## GRINDER 115 MM 900W

- Maximum productivity, speed and safety for all work in tight spaces
- Perfect solution for U-channels and other narrow places
- 900W motor with brushless delivers the right amount of power for all grinding and cutting applications
- Tool-free disc change
- 2-position handle: for use in all orientations. Suitable for right- and left-handed users



Disc Ø (mm): 115  
Power: 900W  
No-load RPM: 0-11800  
Spindle Thread: M14  
Vibration Level (m/s<sup>2</sup>): 11  
Switch: Slide

with multi-position side handle, depth stop, protective guard, 2-position side handle, indoor/outdoor flange, service key

DWE4156-QS

5 035 048 634 479