


Deep groove ball bearings, single row, SKF Energy Efficient (E2) bearings



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
20	52	15	16,3	7,8	0,34	33000	17000	0,14	E2.6304-2Z/C3



Calculation factors

k_r 0,03
 f_0 12