

DCP580P2-QW

Rabot XR 18V 5Ah Li-Ion Brushless



5035048616284

Product Description:

No-load speed (rpm): 0-15000 Planing width (mm): 82 Flange length (mm): 295 Max. cutting depth (mm): 2 Rebate depth (mm): 9



Product features and benefits:

- Powerful brushless motor provides smooth planing performance combined with extended run time Compact, lightweight and ergonomic
- design for better comfort and support during extended periods of use Large double-paddle drum with TCT blades for high-quality surface
- finishes Built-in blade storage and Torx wrench allow for quick blade changes and reduce downtime Important front and support rear for
- better stability Compatible with the AirLock dust extraction system
-
-
- TSTAK® VI Box

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Deflector and Chip Bag (x1)
- Suction adapter (x1)
- Reversible Carbide Irons (x1)
- Parallel fence (x1)
- Torx wrench (x1) Blade alignment plate (x1)
- TSTAK VI box (x1) Multi-voltage charger
- (x1) 5 Ah batteries with charge indicator (x2)
-
-

Specifications techniques :

- ~~Capacity~~ battery: 5 Ah
- Voltage: 18 V
- Power Output : 340 W
- - Maximum Depth of Cut: 2 mm
 - Planing width: 82 mm
 - Drum diameter: 48 mm
 - Hoof length: 295 mm

