

Features

- For use with compressed air in workshops, garages, assembly line and industrial applications.
- Internal steel frame and drum encased in a durable polypropylene outer cover.
- PU Mesh Hose
- Auto lock/Auto rewind
- Automatic Spring Return.
- Adjustable Hose Stop
- 180 ° degree swivel bracket.
- Wall or ceiling mounted.
- Supplied with 1.5m of leader hose.
- For use with air tools, spray equipment, blow guns etc.

RS PRO Family Name

RS Stock No.: 0325314



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO Compact Heavy Duty Air Hose Reel

- For use with compressed air in workshops, garages, assembly line and industrial applications
- Unique Design
- Internal steel frame and drum encased in a durable polypropylene outer cover
- PU Mesh Hose
- Auto lock/Auto rewind
- Automatic Spring Return
- Adjustable Hose Stop
- 180 ° degree swivel bracket
- Wall or ceiling mounted
- Supplied with 1.5m of leader hose
- For use with air tools, spray equipment, blow guns etc.
- Hose is stored safely in a convenient place ready for use

General Specifications

Hose Length	12m
Hose Inner Diameter	8mm
Hose Outer Diameter	12mm
Mounting	Wall Mounted
Inlet Connection	¼" BSP Male
Outlet Connection	¼" BSP Male

Mechanical Specifications

Operating Pressure	Max. 16 Bar
Retraction Operation	Spring Return
Weight	5kg

Specifications

NO	PRODUCT NAME	QTY	NO	PRODUCT NAME	QTY	NO	PRODUCT NAME	QTY	NO	PRODUCT NAME	QTY
1	Spring and spring fastening lock	1	12	Latch lever axle	1	23	Right plastic shell	1	34	NUT M6	1
2	Spring and Shaft connection spring	1	13	one-way latch lever	1	24	SCREW M4x50	2	35	Safety pin	1
3	Spring	1	14	External circlip	1	25	NUT M4	4	36	NUT M12	1
4	Reel inside	1	15	Outlet three way valve	1	26	locating pin spring	1	37	Inlet three way valve	1
5	Axle copper sleeve	1	16	Left plastic shell	1	27	locating pin support	1	38	Inlet pipe	1
6	Reel inside cover	2	17	protective	2	28	locating pin knob	1	39	Inlet three way valve guard	1
7	O RING 16x2.4	2	18	Cross flat head screw M4x14	2	29	Round head cross head screw M3x10	1	40	SCREW 4x16	2
8	O RING 12x2.4	2	19	Round cross head screw M4x12	6	30	Support copper sleeve	2	41	Outlet pipe	1
9	Axle	1	20	roller shaft	2	31	Support	1	42	Stop ball	1
10	Latch lever	1	21	roller	2	32	Screw M6x25	1	43	Screw 5x16	2
11	Latch lever spring	1	22	Positioning pin guide sleeve	1	33	6X35 rod	1	44	Holder	1

