



Brand of NTN corporation

Technical data

UCT204-12

Bearing units




Grey cast housing, radial insert ball bearing with socket set screws, seal with slinger

KIT CONTENT

UC204-12G2, T204

VISUAL (S)



PRODUCT DEFINITION

Brand	SNR
A - Housing width	32 mm
A1 - Width of location slot	12 mm
A2	21 mm
B - Width of Inner Ring	31 mm
d - Shaft diameter	19,05 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

G - Grease fitting	M6x1
H - Housing length, width or diameter	89 mm
H1 - Distance between location slots	76 mm
H2 - Housing height / width	51 mm
L - Housing length	94 mm
L1 - Distance attachment end face to bearing centerline	61 mm
L2 - Thickness of attachment end	10 mm
L3 - Length of guidance slot/face	51 mm
N - Mounting hole dimension	19 mm
N1 - Length of attachment slot	16 mm
N2 - Height of attachment slot	32 mm
S - Distance front side/bearing centre	12,7 mm

PRODUCT PERFORMANCE

C - Dynamic load rating	12800000 mN
C0 - Static load rating	6650000 mN
Operating temperature min.	253,15 °K
Operating temperature max.	373,15 °K

OTHER FEATURES

Mass	0,77 kg
Recommended tightening torque for set screw	3.7 N-m

