

INSULATED PLIER SET FOAM3 7 PIECES



- Approved for live working up to 1,000 volts
- Pliers with TRP grip for a more secure and comfortable grip
- Tools are hold in place using three colour pre-cut high-density EVA foam
- Design to fit exactly in TengTools service cases
- Design and manufactured to DIN and IEC60900
- Designed and manufactured to DIN & IEC60900 standards
- Organised in a foam inlay module size 3 (FOAM3)

Insulated Plier Set FOAM3 7 pieces

General information

Country of origin: Taiwan
Barcode: 5020385072206
Tarriff code Europe: 8205400000
ECCN US: EAR99
ETIM: EC011815
UNSPSC: 27113201

Dimensions

Net weight (g): 1747
Width (mm): 433
Depth (mm): 267
Height (mm): 49

Attributes

Product type: Pliers Sets, Insulated Tool Sets
Certificates: VDE
Number of pieces: 7
Handle type: Bi-material
Insulated: Yes
Inlay material: FOAM
Type of set: FOAM3

Features



**FOAM
SERIES**



Technical changes and errors may occur. 01-08-2024 19:59



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
441 39 Alingsås, Sweden

LIST OF CONTENTS



TEFMBV07 Insulated Plier Set FOAM3 7 pieces

- MBV441-6** Insulated Side Cutting Plier 160 mm
- MBV444-8** Insulated Cable Cutter 210 mm
- MBV451-7** Insulated Combination Plier 185 mm
- MBV461-8** Insulated Long Nose Plier 215 mm
- MBV463-8** Insulated Long Nose Plier Bent 210 mm
- MBV482-10Q** Insulated Water Pump Plier 260 mm
- MBV499-7** Insulated Wire Stripping Plier