

Specifications for Self-laminating Vinyl tape for BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL

Adhesive	Permanent Acrylic
Article No.	110928
Brady Material No.	B-427
Material Type	Self-laminating Vinyl
Colour	Black on White/Transparent
Finish	Matt
Order Reference	M21-1000-427
Printable Area - Height (mm)	4270.00
Printable Area - Width (mm)	9.53
Printer Compatibility	BMP21-PLUS; BMP21
Size - Length (m)	4.30
Size - Width (mm)	25.40
Additional Information	The clear wraparound size is 9.52 mm. Abrasion resistant, Excellent abrasion and smudge resistance, Excellent water & oil resistance, Good moisture resistance, Self-extinguishing, Self-laminating. Not compatible with the ID PAL Printer. Parts will print with black text
Thickness (mm)	0.102
Total Qty per Pack	1 Roll(s) / Box
Wire Gauge	12-10
Approval/Compliance	UL Recognised
Application	Communication Cabling; Panel Identification; Voice & Data Communication; Wire & Cable Marking
Continuous vs Die Cut Labels	Continuous Tape
Industry	Data Communications; Manufacturing; Electrical; Buildings ID
Description	Self-laminating labels.
Max. Service Temp. °C	70
Max. Wire/Cable Diameter (mm)	5.10

Min. Service Temp. °C	-80
Min. Wire/Cable Diameter (mm)	2.70
Surface	For smooth & textured/rough surfaces
Voice/Data Application	Communications Cables