



Save as PDF



**Peli protector cases - Waterproof peli cases - 1550 case**

Interior dimensions:  
46.8 x 35.5 x 19.3 cm (18" x 14" x 8")



**Watertight, crushproof, and dust proof**

- Easy-open, double-step latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve
- Comfortable, rubber over-moulded handle
- Stainless steel hardware and padlock protectors
- 2 layer Pick 'N' Pluck™ foam with convoluted lid foam
- Personalised nameplate service available
- Unconditionally Guaranteed



Black Silver Yellow Orange Desert\_tan

**Peli protector cases - Waterproof peli cases - 1550 case SPECIFICATIONS**

Exterior Dimensions (L x W x D)			Interior Dimensions (L x W x D)		
52.4 x 42.8 x 20.6 cm (21" x 17" x 8")			46.8 x 35.5 x 19.3 cm (18" x 14" x 8")		
Lid Depth	Bottom Depth	Total Depth			
4.4 cm (2")	14.9 cm (5.87")	19.3 cm (7.62")			
Lid Depth	Bottom Depth	Total Depth			
4.4 cm (1.75")	14.9 cm (5.87")	19.3 cm (7.62")			
Weight w/Foam	Weight w/o Foam	Buoyancy Max.			
5.4 kg. (11.9 lbs)	4.8kg (10.58 lbs.)	31.7 kg (69.89 lbs. )			
Range Temperature					
-40 / 99° C (-40 / 210° F)					

Personalized Nameplate Available

**1550 Case Certificates**

- IP67(1 meter submersion for 30 minutes)
- MIL C-4150J
- Def Stan 81-41/STANAG 4280
- ATA 300

**Materials**

Body	Latch	Lid O-Ring	Pins
Polypropylene	ABS	PolymerStainless Steel	
Foam	Purge Body	Purge Vent	Purge O-Ring
1.3 lb Polyurethane	ABS	3 Micron Hydrophobic Non-Woven PET	70 Shore Nitrile

**Configuration**

Cat. #	Description
1550	Peli protector cases - Waterproof peli cases - 1550 case

**Peli protector cases - Waterproof peli cases - 1550 case Accessories**

Cat. #	Description