

Pin Busbar, 10mm² connection: 3p/N (RCCB N-right) 1x RCCB 4-pole + 5x MCB
2-pole touch protected 14 MW fixed length

Model	
product brand name	SENTRON
product designation	Pin busbar
design of the product	10 mm ² , 3p+N, RCCB N right 3p+N, 5x MCB 1p+N, cannot be cut
General technical data	
phase number	3
cross-section	10 mm ²
operating voltage rated value maximum	400 V
Main circuit	
operational current rated value	63 A
Suitability	
suitability for interaction	
• devices with auxiliary switch	No
• devices with N conductor	Yes
Product details	
product feature insulated	Yes
Number	
number of devices suitable for fitting	6
Connections	
type of electrical connection	Pin
Mechanical Design	
module width	18 mm
height	15.2 mm
width	10.7 mm
length	248 mm
net weight	103 g
Approvals Certificates	
General Product Approval	other



[Confirmation](#)

[Miscellaneous](#)



[Miscellaneous](#)

other	Environment
-------	-------------

[Confirmation](#)

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5ST3625-4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5ST3625-4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3625-4

last modified:

7/5/2024 

