

Datasheet

RS Pro ispot[®] Lozenge LED Bulkhead



Description:

The ispot[®] Lozenge driverless bulkhead is the most advanced LED bulkhead on the market. It boasts an attractive ultra-thin design with a depth of only 36mm. The ispot[®] Lozenge driverless bulkhead is tamper proof with no visible screws on the front and tamper proof screws are hidden on the back. Available in Daylight and Warm White with a black or white finish.

Specification:

- Innovative high voltage LED chip – no driver required
- Energy efficient super bright LED
- Daylight and Warm White options
- High grade aluminium body and polycarbonate diffuser
- Impact resistant
- No visible screws on front – Tamper proof screws on back
- Available in Black and White finishes
- 100-230V
- IP65



ENGLISH

Technical Details:

Wattage	Dimensions (mm)	Beam Angle	Lumen Output	Colour Temperature	Finish
10W	220x130x36	110°	600lm	5700K	White
10W	220x130x36	110°	600lm	5700K	Black
10W	220x130x36	110°	600lm	3000K	White
10W	220x130x36	110°	600lm	3000K	Black
20W	220x130x36	110°	1200lm	5700K	White
20W	220x130x36	110°	1200lm	5700K	Black
20W	220x130x36	110°	1200lm	3000K	White
20W	220x130x36	110°	1200lm	3000K	Black

Standards

- BS EN 60598-1+A11
- BS EN 60598-2-1
- BS EN 60598-2-5
- BS EN 62471
- BS EN 62493
- BS EN 55015+A2
- BS EN 61547
- BS EN 61000-3-2+A2
- BS EN 61000-3-3