




Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 966645-5
2x5P HV100 REC. CON, SMD, GOLD,
TUBE PACK



TE Part # 87133-5
10 LOCKING CLIP HSG DR MRKD

Customers Also Bought



TE Part #3-1879335-7
CPF 0603 51R1 1% 50PPM 1K RL



TE Part #6-1879336-1
CPF 0603 976R 1% 50PPM 1K RL



TE Part #826953-2
2P MOD2 STIFT LEI




TE Part #HD34-24-14PN
REC, 14P, AL, N, 4/12/16, P



TE Part #2336568-1
RECEPT ASSY, RA, 168 POS, SLIVER
2.0




TE Part #1676335-1
RN 0805 40K2 0.1% 10PPM CUT
LENGTH



TE Part #1375796-2
PC104 ASY UNKEYED



TE Part #3-2176329-6
CRGP 1210 8K2 1%



TE Part #216906-1
.250 POWER TERM.A.P



TE Part #4-794682-8
18P MICRO MNL ASSY,VRT,THRU,L

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-103801-5_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-103801-5_G.3d_igs.zip

English



Customer View Model
[ENG_CVM_CVM_5-103801-5_G.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.