

S489 - Hi-Vis Contrast Winter Bib and Brace

Collection: 300D Industry High Visibility

Range: High Visibility

Shell Fabric: 300D Industry: 100% Polyester, 300D Oxford, Stain Resistant Finish, Double PU Coated, 190g

Outer Carton: 18

Product information

A garment designed to be completely practical and safe, the Contrast Bib & Brace protects the lower body and chest against wet conditions whilst ensuring safety.

300D Industry High Visibility

A comprehensive range of single and combination garments in a highly durable, EN343 certified fabric including some new cleverly designed and innovative styles.

High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

Standards

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
EN 343 Class 3:1 X (WP 15,000mm)
EN 342 (0.341 (M².K/W), 2, X)
ANSI/ISEA 107 SUPPLEMENTAL CLASS E



Features

- Waterproof with taped seams preventing water penetration
- Extremely water resistant PFAS free Texpel™ Splash Eco fabric finish, water beads away from fabric surface
- EN342 Protection against cold certified up to -36°C
- Adjustable side opening for added flexibility
- Zipped ankles for easy fitting over work boots
- Adjustable straps for a secure fit
- Ergonomic quick release buckle
- Multiple utility pockets providing ample storage
- Back patch pocket
- Double rule pocket
- Elasticated back panel



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

S489 - Hi-Vis Contrast Winter Bib and Brace

Commodity Code: 6203433100

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/13983-03/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
S489YERXS	Yellow	65.0	40.0	58.0	1.1000	0.1508	5036108305223	25036108794267
S489YERS	Yellow	65.0	40.0	58.0	1.1100	0.1508	5036108180158	25036108676679
S489YERM	Yellow	65.0	40.0	58.0	1.1200	0.1508	5036108180141	25036108676662
S489YERL	Yellow	65.0	40.0	58.0	1.2400	0.1508	5036108180134	25036108676655
S489YERXL	Yellow	65.0	40.0	58.0	1.2100	0.1508	5036108180165	25036108676686
S489YERXXL	Yellow	65.0	40.0	58.0	1.2500	0.1508	5036108180172	25036108676693
S489YERXXXL	Yellow	65.0	40.0	58.0	1.2600	0.1508	5036108180189	25036108753417
S489YER4XL	Yellow	65.0	40.0	58.0	1.3500	0.1508	5036108305230	25036108794274