



Symphoni AV

VERSATILE UK & EUROPEAN
FIRE TONES
ULTRA LOW POWER
CONSUMPTION
INTEGRATED 100dB(A)
SOUNDER & BEACON
COMPACT DESIGN BASED
ON THE SYMPHONI
LOCKABLE BASE

Model	Symphoni AV
Nominal Voltage	24Vdc
Current Consumption (tone dependant)	10mA
Sound Output (tone dependant)	100dB
Alarm Tones	Please see datasheet
IP Rating	IP21C
Lens Colour	Red
Flash Rate	1Hz
Beacon Type	LED
Voltage Rating	18 to 30Vdc
Current	10mA max
Volume Control	10dB, by switch
Light Output	>2Cd
Synchronisation	Sounder 100ms over 30min/Light 20ms over 30min
Flash Colour	Red
Monitoring	Diode (reverse polarity)
Temperature Range	-10 degrees C to +55 degrees C
Base Lock	Latch - key supplied