

## KSW 18 FANS

### WALL FAN



The KSW18W Wall Fan provides powerful air movement to area's most needed, therefore creating a comfortable environment.

Designed to be used in a wide variety of domestic , commercial and industrial applications.

3 precision balanced metal fan blades to provide economical cooling and air circulation.  
90° oscillating sweep helps cover larger areas for optimum cooling.

#### Features and Benefits:-

- The fan is easy to install with mounting brackets and screws included.
- Easy to control as it has a combination of a pull cord system and rotary dial to regulate fan speed (1-3, with 0 being off).
- The fan blades are constructed with high quality aluminium and fully balanced
- The high performance motor has built in thermal cut out protection.
- Guards are closely meshed black painted wire with additional radial support to provide increased stiffness.

### PEDESTAL FAN



The KSW18P Pedestal Fan provides powerful air movement to area's most needed, therefore creating a comfortable environment

Designed for domestic and commercial applications, this sturdy, portable fan provides continuous high flow air movement for ventilation or cooling. Users can adjust heights and the large 20" diameter pedestal base aids for extra safety and stability. Strong and quality build will give you years of trouble free service.

#### Features and Benefits:-

- 3 fan speeds
- 90° oscillating sweep helps cover large areas for optimum cooling.
- 3 blade high velocity impellor.
- Large hand screw to allow for height adjustments.
- Durable all-steel construction.
- Large 20" diameter pedestal base for added safety and stability.
- Tilt facility.

### Specifications KSW18W and KSW18P

Fan diameter	18 inches
Fan diameter	450 mm
Air flow	6100 m <sup>3</sup> /hr
Noise Level	50 dBA
Weight	9 kg
Voltage	240 v
Wattage	N/A
Plug/Fuse	UK BS1363/13A