

General description

Tecbond 239 is an exceptionally clear economic general purpose adhesive. It is high in viscosity and has a medium open time. It provides good bonds on wood, paper, card, and many other surfaces. Being high viscosity it is an excellent gap filler and ideal on many fabrics and foams that are porous.

Technical characteristics

Adhesive type: Synthetic polymer based hotmelt
 Colour: Clear
 Molten tack: Medium

	7mm	12mm	15mm	43mm
Form	7.0mm x 150mm	11.5mm x 300mm	15mm x 300mm	43mm x 43mm
Sticks per kilo (approx)	160	34	20	17
Carton quantity	14kg	5kg	5kg	10kg
Pallet weight:	500kg	500kg	500kg	500kg
Suggested application	195°C	195°C	195°C	195°C
Brookfield viscosity (POW-12-VISC) spindle 27	18,000 cps	18,000 cps	18,000 cps	18,000 cps
Ring & ball softening point (ASTM E28)	84°C	84°C	84°C	84°C
Heat resistance (BS5350 Part 1)	70°C	70°C	70°C	70°C
Open time	Medium	Medium	Medium	Medium
Low temperature flexibility (tg)	-30°C	-30°C	-30°C	-30°C

F.D.A. approved. All the constituent parts of this adhesive have been approved by the American F.D.A. under C.F.R. 21.175.105 (adhesives) (subject to limitations).

Tecbond Reference	Description	12mm	15mm	43mm	CT	Bulk
5	High delivery, low viscosity, long open time. Product assembly adhesive.	●		●	●	●
14	High delivery, vary fast setting packaging adhesive.	●	●	●		
1942	Product assembly adhesive for wood and many plastics.	●	●	●		
1X	Low viscosity, wood working & packaging adhesive. Medium open time.	●		●		
213	Economical, general purpose adhesive.	●	●	●		
214	Economical, fast setting, packaging adhesive.	●	●	●		
23	Medium viscosity multipurpose adhesive.	●	●	●		
232	Economical, clear, general purpose adhesive.	●	●	●		
232 Glitter	Multicolour, Red, Green, Silver, Gold.	●				
240	High delivery, long open time, multipurpose, clear adhesive.	●	●	●		
240 Coloured	Coloured, medium open time, general purpose adhesive. Brown, Green, White, Black, Blue, Gold, Silver, Red, Orange, Yellow.	●				
246	Clear and black versions, high performance, gap filling, difficult surfaces, dent pulling.	●				
260	High performance, long open time, tough, flexible adhesive.	●	●	●		
265	Long open time product assembly adhesive for smooth and shiny surfaces.			●		
267	High heat resistant, medium open time, product assembly adhesive.			●		
2169	Peelable adhesive, low tack, non-migrating, CD & credit card attachment, glue dots.				●	●
342	High viscosity, fast setting, white adhesive.	●		●		
410	Pallet stabilisation spray adhesive			●		
420	General purpose spray adhesive.			●		
425	High delivery, high performance, spray adhesive.			●		
430	High performance, long open time spray adhesive.			●		
4741	Full pressure sensitive, very aggressive, multipurpose, paper & plastic materials.				●	●
7718	Coloured, low viscosity, potting, encapsulation & knot filling / wood repair polyamide adhesive.	●	●			
7784	High temperature resistant multipurpose polyamide adhesive.	●	●	●		
7785	High temperature & chemical resistant multipurpose polyamide adhesive.	●	●	●		
9010	Reactive hotmelt. Heat & chemical resistant bonds, rigid bond, once set does not reactivate with heat.				●	
9030	Reactive hotmelt. Heat & chemical resistant bonds, flexible bond, once set does not reactivate with heat.				●	
LM44	Lowmelt, fast setting, high performance, white adhesive.	●		●		

- Storage** Store in a clean dry place at temperatures between 5°C and 30°C with boxes closed. Do not expose to direct sunlight or localised heat sources such as radiators or hot pipes.
- Removal of glue** Assembled components can be separated by heating assembly to a temperature slightly above the heat resistance figure.
- EVA & Polypropylene: Residues of EVA and polypropylene based hotmelts can be removed from components with white spirit.
- Polyamide: Residues of polyamide based hotmelt can be removed from components with acetone.
- PUR: Prior to cross linking adhesive can be removed with white spirit or ketone. Once fully cross linked the adhesive cannot be easily removed.
- Please note** The information contained on this data sheet is for guidance only. It is the result of careful laboratory evaluations by trained and qualified staff using British Standard or similar test methods. However, no warranty is expressed or implied regarding the accuracy of the data or the suitability of the adhesive for any specific purpose. In every case, we strongly recommend that the user shall make their own test to determine to their own satisfaction the suitability of the adhesive for their particular purpose. Neither the seller nor manufacturer shall be liable for any injury, loss, damage, direct or consequential arising out of the use or inability to use the product. Further information is always available to help solve your adhesive problems. Should you require any further information on our adhesives please contact your nearest distributor.