

ENGLISH

Datasheet

Stock No: 383-721

RS Pro 4 Core Unscreened Grey PVC Industrial Cable, 250 V



Product Details

Core construction 7 x 0.25 mm (0.34 mm²)

Unshielded LiYY

Fine-strand copper wire with PVC insulation

Colour and strand coding in accordance with DIN 47100

Cores stranded in layers

PVC outer sheath, grey (RAL 7000)

Operating temperature -5°C to +80°C





Specifications

Number of Cores	4
Cross Sectional Area	0.34 mm²
Screened/Unscreened	Unscreened
Length	100m
Outer Diameter	5.4mm
Sheath Colour	Grey
Core Strands	7/0.25 mm
American Wire Gauge	22 AWG
Voltage Rating	250 ∨
Sheath Material	Polyvinyl Chloride P√C
Number of Strands	7
Cable Shape	Multicore
Minimum Bend Radius	10 x D
Size of Strands	0.25 mm
Conductor Material	Copper
Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-5°C
Conductor Resistance	55 Ω/km
Insulation Material	PVC