

3U 19in Steel Vertical Wall Mount Equipment Rack Bracket

Product ID: RK319WALLV



The RK319WALLV 3U 19in Steel Vertical Wall Mount Equipment Rack Bracket offers a versatile storage solution, allowing equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 3U bracket can be installed under a desk for horizontal installation, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Constructed to EIA-310 19in rack standards, the wallmount bracket features a sturdy steel design, perfect for SoHo (small office, home office) environments. The wallmount bracket offers space-saving installation for environments lacking the footprint space for a full size server equipment rack.

Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes (used to mount to a wall or the desk underside) are positioned at exactly 16in apart, matching standard construction framework.

Backed by a StarTech.com lifetime warranty.

Need more storage space? StarTech.com also offers a [1U 19in Wallmount Bracket](#), a [2U 19in Wallmount Bracket](#) and a [4U 19in Wallmount Bracket](#).

Certifications, Reports and Compatibility



Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

Features

- Constructed to meet the EIA-310 19" rack standards
- Arrives fully assembled with cage screws and nuts for mounting equipment into the rack
- TAA compliant for GSA Schedule purchases
- Equipment can be vertically wall mounted, or horizontally under a desk
- Compatible with most 19" rack mountable equipment
- Made from solid steel for durability
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs

Hardware	Warranty	Lifetime
	Frame Type	Open Frame
	Industry Standards	EIA/ECA-310-E
	Mounting Hole Types	Square (For Cage Nut)
	Mounting Rail Profile	L-Shape
	Rack Type	2-Post
	U Height	3U
	Wallmountable	Yes
Performance	Weight Capacity	125.3 lb [56.7 kg]
Special Notes / Requirements	Note	Package includes 1 ½" screws for mounting to wood surfaces, additional hardware will be required for other materials
Physical Characteristics	Color	Black
	Construction Material	Steel
	Enclosure Type	Steel
Product Measurements	Product Height	5.9 in [14.9 cm]
	Product Length	5.9 in [15.1 cm]
	Product Width	19.8 in [50.3 cm]
	Weight of Product	32.5 oz [921 g]
Packaging Information	Flat Pack (Assembly Required)	No
	Package Height	6.3 in [16 cm]
	Package Length	20.4 in [51.8 cm]
	Package Width	6.5 in [16.5 cm]
	Shipping (Package) Weight	3 lb [1.4 kg]
What's in the Box	Included in Package	1 - Vertical Wall Mount Bracket
		12 - M5 Screws
		12 - M5 Cage Nuts
		6 - Wood Screws
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.