

WP-STEEL PVC C 36 - Protective hose



3240872

<https://www.phoenixcontact.com/in/products/3240872>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: Steel, galvanized / PVC, degree of protection: IP68, color: black, inside diameter: 29 mm, Total length: 10 m

Commercial data

Item number	3240872
Packing unit	1 m
Minimum order quantity	1 m
Sales key	BF7
Product key	AF7DSA
Catalog page	Page 600 (C-3-2019)
GTIN	4046356737371
Weight per piece (including packing)	999.9 g
Weight per piece (excluding packing)	999.9 g
Customs tariff number	83071000
Country of origin	DE

WP-STEEL PVC C 36 - Protective hose



3240872

<https://www.phoenixcontact.com/in/products/3240872>

Technical data

Notes

Notes on operation	Protective hose length is measured stretched out; length tolerance $\pm 5\%$
--------------------	--

Product properties

Product type	Protective hose
Tensile strength GRP	500 N

Dimensions

Internal dimensions

Internal diameter	29 mm
-------------------	-------

Material specifications

Material	Steel, galvanized / PVC
----------	-------------------------

Cable/line

Bending radius, dynamic	225 mm
Bending radius, static	90 mm
Tensile strength	500 N
Halogen-free	no

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-25 °C ... 90 °C
Short-term temperature	100 °C


WP-STEEL PVC C 36 - Protective hose



3240872

<https://www.phoenixcontact.com/in/products/3240872>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/3240872>



VDE approval of drawings

WP-STEEL PVC C 36 - Protective hose



3240872

<https://www.phoenixcontact.com/in/products/3240872>

Classifications

ECLASS

ECLASS-11.0	27430301
ECLASS-12.0	27430301
ECLASS-13.0	27430301

ETIM

ETIM 9.0	EC001179
----------	----------

UNSPSC

UNSPSC 21.0	40141700
-------------	----------

WP-STEEL PVC C 36 - Protective hose



3240872

<https://www.phoenixcontact.com/in/products/3240872>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

WP-STEEL PVC C 36 - Protective hose

3240872

<https://www.phoenixcontact.com/in/products/3240872>



Accessories

WP-SC BRASS WP PVC 36 - Cable protection end sleeve

3241077

<https://www.phoenixcontact.com/in/products/3241077>

End sleeves as cable protection, made of brass, for WP-STEEL PVC C



WP-G BRASS IP65 PG29 - Protective hose screw connection

3241056

<https://www.phoenixcontact.com/in/products/3241056>

Cable gland made from brass with Pg thread, IP65 protection



WP-STEEL PVC C 36 - Protective hose

3240872

<https://www.phoenixcontact.com/in/products/3240872>



WP-G BRASS IP65 M32 - Protective hose screw connection

3241063

<https://www.phoenixcontact.com/in/products/3241063>

Cable gland made from brass with metric thread, IP65 protection



WP-BASE HF 37 - Hose clamp

3240972

<https://www.phoenixcontact.com/in/products/3240972>

Hose clamp, material: Steel, galvanized, color: black/silver



WP-STEEL PVC C 36 - Protective hose

3240872

<https://www.phoenixcontact.com/in/products/3240872>



WP-BASE A PG29 - Protective hose fixing bracket

3241081

<https://www.phoenixcontact.com/in/products/3241081>



Fixing bracket for protective sleeves, fixed with two screws

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in