



Figure similar

transformer SITAS; phases: 1; Pn/Pn(S6)(kVA): 0.145 /0.49;
Upri(V): 230+/-5%; Usec(V): 110; Isec(A): 1.32; F(Hz): 50...60;
vector group/shielding winding: II0 /0; temperature rise/insulation
class: 40 /B; IP23; connection: screw/flat-type connection;
mounting: screws; EN 61558-2-1, -2-2, -2-4 >UL/CSA-recognized<
>control transformer< >isolation transformer<

General technical data		
product designation		transformer SITAS
product brand name		SIDAC
operating apparent power rated value	VA	145
efficiency		0.86
connection method for transformers		II0
certificate of suitability		CE / cRUus
product function		
• temperature monitoring		No
• insulation monitoring		No
• short-circuit and overload proof		No
number of shielding windings		0
short-term vector power	VA	490
relative short-circuit voltage	%	7.7
Inputs		
phase number of the inputs		1
input voltage		
• _1 rated value	V	242
• _2 rated value	V	230
• _3 rated value	V	218
electrical input frequency		
• minimum	Hz	50
• maximum	Hz	60
Outputs		
phase number of the outputs		1
output voltage		
• _1 rated value	V	110
electrical output frequency		
• maximum	Hz	60
• minimum	Hz	50
Ambient conditions		
thermal class according to IEC 60085		B
ambient temperature rated value	°C	40
protection class IP		IP23
Mechanical data		
type of electrical connection		
• at output for main current circuit		screw-type terminals / tab terminals
• at input for main current circuit		screw-type terminals / tab terminals

fastening method		screws
construction form of the iron core		EI 96/44
width	m	0.244
height	m	0.245
depth	m	0.23

Certificates/ approvals

General Product Approval	other	Environment
--------------------------	-------	-------------



[Confirmation](#)

[Environmental Confirmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>
Information for data generation and storage
<https://support.industry.siemens.com/cs/ww/en/view/109995012>
Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>
Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=4AM3842-4TJ10-0FC0>
Cax online generator
<https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=4AM3842-4TJ10-0FC0>
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/4AM3842-4TJ10-0FC0>
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=4AM3842-4TJ10-0FC0&lang=en

last modified: 4/2/2025