



Technical data

1R40X50X22

Inner rings

Needle roller bearing, inner ring

PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	40 mm
B - Bearing/Inner ring width	22 mm
F - Under roller diameter	50 mm
rs - Min fillet radius	1 mm
Lubrication hole on inner ring	Non/No
t - IR chamfer length	2 mm
Precision class	P0
Mass	0,118 kg

ABUTMENT	
da min - Min shoulder diameter IR	45 mm
ras max - Max shaft & housing fillet radius	1 mm