



Product data sheet

Power tools for trade & industry

All-purpose Extractor

PRO GAS 12-40 MA



Non-stop work with high protection

The most important data

Weight	14.1 kg
Container volume, net	28 l

Part Number 0 601 9M0 170

Technical data

Technical data

Rated input power	1,200 W
Weight	14.1 kg
Container volume, gross	40 l
Container volume, net	28 l
Container volume, net, water	20 l
Dust class of wet/dry extractor	M
Dust class	M
Filter surface area	3,200 cm ²
Airflow rate (turbine)	71.5 l/s
Vacuum pressure (turbine)	230 mbar
Wheels, number	4
Packaging dimensions (width x length x height)	389 x 670 x 536 mm
Voltage, electrical	230 V
Filter cleaning system	AFC
Anti-static hose	Yes
Antistatic system	Yes
Line input power turbine, max	1,200 W

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- High protection for you against dust penetration ensured with M-Class certified filtering system
- Continuous strong suction power ups productivity and sound disturbance reduced with Bosch own exclusive adaptive Automatic Filter Cleaning (AFC) technology
- Emptying dust container is quicker and easier thanks to hose-less container design and standalone, anti-tipping motor head
- Effortless transportation across sites thanks to telescopic handle and L-Boxx compatibility
- Saves storage and makes lifting easier with integral hose storage design

**HEAVY
DUTY**

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

