



Brand of NTN Group

## Technical data

### UC218-56G2

Insert bearings



Spherical outer diameter, fixing by socket set screw, seal with slinger

#### VISUAL (S)



#### PRODUCT DEFINITION

<b>Brand</b>	SNR
<b>B - Width of Inner Ring</b>	96 mm
<b>C - Width of Outer Ring</b>	37 mm
<b>C1 - Distance center of OR to center of lubrication zone</b>	12 mm
<b>d - Shaft diameter</b>	88,9 mm
<b>D - Outer diameter of OR</b>	160 mm
<b>G - Set screw size</b>	1/2-20UNF
<b>m - Distance to set screw</b>	14 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

### PRODUCT DEFINITION

<b>r - Radius Inner Ring</b>	2
<b>S - Distance front side/bearing centre</b>	39,7 mm
<b>f0 - Factor</b>	14.4
<b>SW - Wrench size</b>	6,35 mm

### PRODUCT PERFORMANCE

<b>C - Dynamic load rating</b>	96000000 mN
<b>C0 - Static load rating</b>	71500000 mN
<b>Operating temperature min.</b>	253,15 °K
<b>Operating temperature max.</b>	373,15 °K

### OTHER FEATURES

<b>Mass</b>	4,56 kg
<b>Recommended tightening torque for set screw</b>	33.9 N-m

### BEARING FREQUENCIES

<b>BPFO - Over rolling frequency on outer ring (60 rpm)</b>	4.111 Hz
<b>BPMF - Over rolling frequency on inner (60 rpm)</b>	5.889 Hz
<b>BSF - Over rolling frequency on rolling element (60 rpm)</b>	5.44649696287964 Hz
<b>BRF - Rotational frequency - rolling element (60 rpm)</b>	2.72324848143982 Hz
<b>FTF - Rotational frequency - cage (60 rpm)</b>	0.4111 Hz

