Product data sheet
Characteristics

TM171DLED
Modicon M171 Optimized Display LED

Local Stock Code: Not on Stock



Main

Range of product	Modicon M171
Product or component type	Display module
Display colour	Monochrome
Supply	External source

Complementary

Display type	7 segments LED + decimal point
Number of key	8
Colour	Grey
[Us] rated supply voltage	12 V DC
Power consumption in W	5 W 0 W
Marking	CE
Local signalling	LED
Product compatibility	Logic controller M171 optimized
Height	74 Mm
Width	32 Mm
Depth	30 Mm
Product weight	0.042 Kg

Environment

Product certifications	cURus
IP degree of protection	IP20

Ordering and shipping details

Category	US1PC1222537
Discount Schedule	PC12
GTIN	3606480752643
Returnability	No
Country of origin	IT

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	13.000 Cm
Package 1 Width	9.000 Cm
Package 1 Length	12.700 Cm
Package 1 Weight	129.000 G
Unit Type of Package 2	S01
Number of Units in Package 2	5
Package 2 Height	15.000 Cm
Package 2 Width	15.000 Cm
Package 2 Length	40.000 Cm
Package 2 Weight	725.000 G

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is k
Mercury free	Yes
Sustainable packaging	Yes
Packaging made with recycled cardboard	Yes
REACh Regulation	Reference contains Substances of Very High Concern above the threshold
EU RoHS Directive	Compliant By Exemption
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and neve

Contractual warranty

Warranty (in months)	18

Product Life Status : End of commerc. announced

TM171DLED may be replaced by any of the following products:



TM173DLED

Remote Display, Modicon M171/M172/M173, flush mounted optimized display

Qty 1

Substitution date: |