



Datasheet

Stock No: 858-893

ENGLISH

RS Pro Black Rubber Tyred Wheel WAT8RBM20, 75kg



Product Details:

Black Pneumatic Tyred Wheel

- Tubed 2-ply pneumatic rubber tyre can be inflated to 2.5 bar
- 20mm steel hub with roller bearing

Note: Wheel size refers to the size of wheel hub plus tyre

Industrial - Pneumatic Tyred Wheel

Pneumatic wheel are excellent for shock absorbing and work well on difficult surfaces like grass, gravel and rough, uneven, surfaces.

Specifications:

Load Capacity:	75kg
Tyre Type:	Pneumatic
Tyre Material:	Rubber
Hub Material:	Steel
Features:	Shock Absorbing
Hub Bearing Type:	Roller Bearing
Wheel Diameter:	196mm
Wheel Width:	48mm
Bore Diameter:	20mm
Bore Length:	60mm
Colour:	Black