

CAB CAB PC 604022 G3B



Sample photo

Order symbol: CAB PC 604022 G3B
Product nbr: 8113372
Description: Cabinet, PC
Remarks: Locks on the long side

EAN: 6418074020468
El. number:
 Finland: 3424128
 Denmark: 8212019289
 Italy: 7821070
 Sweden: 2539985

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

| Dimensions: | | Length | Width | Height | Rating: |
|-------------------------|--|----------------------------|-------|--------|--|
| mm: | | 600 | 400 | 220 | Ingress Protection (EN 60529): IP 65 |
| inch: | | 23.6 | 15.7 | 8.7 | Impact Resistance (EN 62262): IK 08 |
| Materials: | | | | | Electrical insulation: Totally insulated |
| Material: | | Polycarbonate | | | Halogen free (DIN/VDE 0472, Part 815): Yes |
| Base colour: | | RAL 7035 | | | UV resistance: UL 508 |
| Cover colour: | | RAL 7035 | | | Flammability Rating (UL 746 C 5): UL 94 5V |
| Gasket material: | | EPDM | | | Glow Wire Test (IEC 695-2-1) °C: 960 |
| | | | | | UL Type: UL TYPE 1, 4, 4X, 12, 13 |
| Temperatures: | | | | | Certificates: |
| Short term: | | -40 ... 120 °C | | | Germanischer Lloyd (GL) |
| Continuous: | | -40 ... 80 °C | | | Underwriters Laboratories |
| Short term: | | -40 ... 250 °F | | | Fimko |
| Continuous: | | -40 ... 175 °F | | | Lloyds Register of Shipping (LR) |
| Accessories: | | | | | Europe EN 50298: 1998 |
| EKIV 64H | | Mounting plate | | | UL Canada |
| EKIV 37 | | DIN-35 Mounting rail | | | Gost R |
| DS35370E1 | | DIN-35 Mounting rail | | | |
| FP A 64 | | Swing-out door/Front plate | | | |
| MB 12225 AL | | Swing door set | | | |
| FP 64 | | Front plate | | | |
| FP 18x3-64 | | Front plate | | | |
| DRF 63/64 | | DIN rail frame set | | | |

