

## Gigaset SL930A

*More than just a cordless DECT home phone:  
Enjoy the comfort of home telephony.  
Experience Android functionality.*



### USP:

- **Android OS with direct access to all (relevant) applications**
- **Cordless DECT telephony with Gigaset high end functionality**
- **Use the successful High End Design of SL910**

Interface: a/b (analog), WLAN 2.4 GHz 802.11 b/g/n  
 Implementation: HA/PBX  
 Standards: DECT, GAP, WLAN 2.4GHz 802.11 b/g/n client  
 Configuration: Connection of 1 external line  
 System: Cordless telephone for up to 6 handsets

### Simple. Beautiful. Useful

Multitasking Operating System  
 Home screen folders and favorites tray  
 Resizable widgets  
 Improved txt input and spell-checking

### Applications

#### Android 4.0.4 Apps

Phone	Adapted Gigaset DECT Telephony
Contacts	Addressbook with full featureset
Settings	Settings to be adapted
Browser	Generic Android Browser
Calculator	
Clock	Analogue clock with widget and timer
Downloads	
Email	Android E-Mail App
Gallery	Foto and Videogallery
Music	MP3-Music player
Search (Google)	Yes
Speech Recorder	Yes
Bookmarks (Widget)	

#### Preinstalled Google Apps

Google Play™	Access to Apps
Google Maps™	Worldwide Map
Google Mail™	Mail
Google+™	Community App
Google Voice Search™	
Google translate™	(with handwriting support) Translate and read texts
Latitude	Find friends and Family in Maps
Google Talk™	Internet Telephony

#### Preinstalled Apps

Gigaset Help	User Manual and Service App
Youtube™	Video-App

### Key Benefits

- Android 4.0.4 Operating System
- Comfort DECT Base station
- Comfortable DECT telephony with access to Android Apps and Internet via WLAN

### Facts

Operating system	Google™ Android 4.0.4 (Ice Cream Sandwich)
Display	Colour TFT-VA touch screen
Resolution	320x480 pixels Size 3.2"
Memory	Internal phone storage 4 GB Expansion Slot microSD™ card, up to 32 GB (microSD™ card not included)
Battery	Lilon 3.7V, 1300 mAh Typical

### Communication

Call list  
 Conference calls via Fixed Net or VoIP  
 Google Talk™ application  
 Speakerphone with Handsfree talking

### Connectivity

3,5 mm audio jack (for stereo headset and micro)  
 Media Transfer Protocol support  
 Micro USB support  
 Synchronisation via Google™  
 Synchronisation via Exchange ActiveSync®  
 USB High speed 2.0 support  
 WLAN 2,4 GHz IEEE 802.11b/g/n

### Design

Auto rotate  
 On-screen 12 key keyboard  
 On-screen QWERTY keyboard  
 Picture wallpaper  
 Touch screen  
 Wallpaper animation

### Disability support

Android 4.0.4 is designed for accessibility:  
 TalkBack (screen reader)  
 Explore by touch (together with Talk Back)  
 Accessibility settings

## Email

Bearer type (IP)	WLAN 2,4 GHz IEEE 802.11b/g/n
Protocols	POP3 and IMAP4
Push email	Microsoft® Exchange ActiveSync® (EAS)
Secure email	SSL/TLS, both port methods (POPS/IMAPS) and START-TLS
HTML mail	Yes (read only)

## Entertainment

Gallery with Media browser  
managing photos and videos  
powerful photo editor included

Video streaming  
YouTube™

## Internet

Bookmarks  
Google Play™  
Google™ Search  
Google Maps™ for Android  
Web browser (WebKit™)

## Messaging

Conversations  
Email  
Google Mail™

## Music

Album art  
Music Player

## Organiser

Alarm Clock  
Calculator  
Calendar

**Contacts** with large picture profile  
phone numbers, addresses, accounts  
status updates, events, button for connected to integrated social network  
"Own" contact information in "Me" profile  
Shortcuts to phone numbers, text messaging

E-Manual (in Help-App)

## Speech recognition and Synthesis

Powerful voice input engine  
Google Voice Search

## Web browser

Browser version	Android 4.0.4 Browser (Based on WebKIT™)
Navigation/rendering	Pan & Zoom Landscape/portrait rendering Full page PC rendering
Search	Internet Search

## Answering machine features via AM-app

- o Integrated answering machine with up to 55 minutes recording time (for long play quality); up to 15 minutes recording time by using brilliant ADPCM quality
- o Simple usage via handset
- o User defined and predefined announcement (170 sec.)
- o Display of new messages on handset
- o Announcement of date and time for each message by voice<sup>2)</sup>
- o ICM Recording time adjustable: unlimited, 1/ 2/ 3 minutes, unlimited
- o Call acceptance adjustable: immediately, automatic, after 10, 20, 30 sec.
- o Call pick up function to answer calls during message recording
- o Recordings have unlimited protection against power failure
- o PIN-protected remote control of answering machine

## Sound quality

- o HDSP™ Ready<sup>1, 2)</sup> handset
- o HSP™
- o Hands-free talking with brilliant sound quality
- o Adjustable volume of handset sound
- o High-quality polyphonic ringer melodies, volume adjustable and on/off function via hard key (long press)
- o Ringer melody output via hands-free speaker
- o Advisory tones (for key tones, confirmation and low battery)

## Convenience – phoning essentials

### Range (DECT/WLAN)

- o Indoor range: up to 50/30 meters
- o Outdoor range: up to 300/100 meters

### Operation time

- o Talk time: up to 20 hours
- o Standby time: up to 110 hours

## Phonebook and dialing

- o Android Contact List for more than 2000 entries
- o Automatic sync with Google contacts via WLAN
- o Name indication for incoming/outgoing/missed calls, redial list (by comparison with contact list)
- o Direct access to outgoing line via off-hook key (long press)
- o Dial preparation (input of phone numbers before connecting) with possibility to correct dial digits
- o Redialing of the 20 last different numbers
- o Dialing: DTMF, pulse, flash (programmable)

## Receiving Calls

- o Caller indication displayed via CLIP and CNIP displayed<sup>2)</sup>
- o 21 ringer melodies, melody upload (via microSDCard)
- o Vibracall
- o Individual ringer melodies for phone book entries and for internal calls

## Missed Calls

- o Signaling via MWI LED above Display
- o List showing up to 20 missed calls with caller indication (CLIP / CNIP - base station required) and time<sup>2)</sup>
- o Direct dialing out of the missed calls list

## Connectivity

- Base station:
- o DECT for up to 6 Handsets
  - o 1 analogue line interface

## General additional features

- o Plug & Play (unpack, connect the phone, call)
- o Stand alone base station
- o Easy access to call lists via touch key in idle screen (access to all calls, outgoing, accepted or missed calls)
- o Date and time functions are protected against power failure
- o Internal antennas

## Menu features

- o Android User-Interface (Ice Cream Sandwich) in all not telephony centric parts
- o Telephony in Gigaset SL910 style
- o User Interface in 48 supported languages

## Keypad features

- o High-quality illuminated keypad with 5 hard keys: illuminated send/talking key (green), back, menu, home key and end/off key (red – with LED).
- o Touch keys with num pad and alpha pad just as needed

## ECO DECT

- o Up to 60% less energy consumption<sup>2)</sup> thanks to an energy-saving power supply
- o ECO Mode - manual reduction of transmitting power by 80%<sup>3)</sup>
- o ECO Mode Plus<sup>4)</sup> for 100% reduction of transmitting power of base station and all registered handsets
- o Variable reduction of transmitting power according to distance between handset and base station

## Accessories

- o Up to 6 Gigaset handsets
- o Gigaset QuickSync allowing sync with Google contacts in the cloud (only for other handsets, providing USB-drivers)

## Features with more than one handset

- o Free internal calls between handsets
- o 2 calls simultaneously (1 external, 1 internal)
- o Ringing assigned to all or selected handsets for internal calls
- o Internal transfer of external calls to another handset with prior consultation call

- o 3 party conference (1 external / 1 internal participants) via internal recall or barge in
- o Collective ringing on incoming external calls

## Fixed net operator features

- o Support of provider features by use of Flash key, \*key and # key

## Technical data

### Handset

- o Standby time: up to 110 hours
- o Talk time: up to 20 hours
- o Battery: Li-Ion ca. 1300mAh
- o Charging time: ~4 h in charger
- o Indoor range: DECT/WLAN up to 50/30 meters
- o Outdoor range: DECT/WLAN up to 300/100 meters
- o Dimensions H x W x D / weight (incl. batteries)  
Handset: ~134mm x 58mm x 16,5mm / 147g (incl. battery/ 174g)

### Base Station / AM Base Station

- o Power-saving 230 V switch-mode power supply
- o Wall mountable
- o Paging key on front of base station
- o Operation of AM through handset
- o Connection of 1 external line
- o Connection of up to 6 handsets
- o Dimensions H x W x D / weight  
Base/ AM base: 115mm x 117mm x 45mm / 126g (without power supply & telephone cable)

### External charger (for Systems & HS Bundles)

- o Presenter design, black glossy front
- o Dimensions H x W x D / weight  
Charger: 33mm x 74mm x 57mm / 98g

### Package contents

- o 1 handset
- o 1 base station
- o 1 Li-Ion battery
- o 1 charger
- o 1 power supply for charger
- o 1 rear cover for handset
- o 1 power supply for base
- o 1 telephone cord
- o 1 short user manual

### Colour

- o black

### Market Introduction UK

- o Market launch in Q4/2013

1) Dependent on country / network/ operator

2) Compared to the previous generation of Gigaset base stations

3) For all registered handsets – in comparison to when ECO Mode is not activated and to our conventional cordless phones

4) When handset is idle or charging and when all registered handsets support ECO Mode Plus