

## Sensor/actuator box - SACB-6/ 6-L-M23 180 - 1692695

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator box, Connection method: M12 socket Plastic, Number of slots: 6, Number of positions: 4, Slot assignment: Single, Status indication: Yes, pnp; Master cable connection: M23 plug connection 180°, Shielding: No

The illustration shows a version with 8 slots

### Why buy this product

- Safety in the field, thanks to molded housing and high degree of protection
- Flexible, distributed bundling of signals in one master cable
- Convenient: increased machine availability thanks to quick and easy diagnostics



### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 177768
Weight per Piece (excluding packing)	126.3 g
Custom tariff number	85366990
Country of origin	Poland

### Technical data

#### General

Rated voltage	24 V DC
Max. operating voltage $U_{max}$	30 V DC
Current carrying capacity per I/O signal	2 A
Current carrying capacity per slot	4 A
Total rated current	12 A
Number of positions	4
Number of slots	6
Inflammability class according to UL 94	V0
Sensor/actuator connection system	M12 socket

#### Ambient conditions

Degree of protection	IP65
----------------------	------

# Sensor/actuator box - SACB-6/ 6-L-M23 180 - 1692695

## Technical data

### Ambient conditions

	IP67
Ambient temperature (operation)	-20 °C ... 75 °C

### Local diagnostics function

Local diagnostics	Supply voltage Green LED
	Status display I/O Yellow LED

### Master cable data/connection data

Connection method	M23 plug connection
Tightening torque slot sensor/actuator cable	0.4 Nm

### Insulation material

Housing material	PA
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	PA
Material of contact, master cable side	CU alloy
Material of contact surface, master cable side	Gold-plated
Material of threaded sleeve	Zinc die-cast
Material, O-ring	NBR

### Pin assignment

Slot/position = Wire color or connection	1 / 4 (A) = 1
	2 / 4 (A) = 2
	3 / 4 (A) = 3
	4 / 4 (A) = 4
	5 / 4 (A) = 5
	6 / 4 (A) = 6
	1-4 / 1 (+ 24 V) = 11
	1-4 / 3 (0 V) = 9+10
	1-4 / 5 (PE) = 12

## Classifications

### eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27449001

# Sensor/actuator box - SACB-6/ 6-L-M23 180 - 1692695

## Classifications

### ETIM

ETIM 2.0	EC000200
ETIM 3.0	EC001856
ETIM 4.0	EC002585
ETIM 5.0	EC002585

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

### Approvals

---

#### Approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized

---

#### Ex Approvals

---

#### Approvals submitted

---

## Approval details

UL Recognized	
mm <sup>2</sup> /AWG/kcmil	22-16
Nominal voltage UN	24 V

cUL Recognized	
mm <sup>2</sup> /AWG/kcmil	22-16
Nominal voltage UN	24 V

## Sensor/actuator box - SACB-6/ 6-L-M23 180 - 1692695

### Approvals

GOST

cULus Recognized

### Accessories

#### Accessories

#### Assembly tool

Pipe spanner - PLUSCON-RCS - 1665062



Special pipe spanner, tool for mounting the M23 connector housing (with assembly), for coupling and sleeve housing

---

#### Circular connector (cable-side)

Cable connector - CA-12S1N8A8007 - 1619708



Cable connector, straight, Shielded, Screw locking, M23, Number of positions: 12, Type of contact: Socket, Crimp connection, Cable diameter: 6 mm...10 mm

---

Cable connector - CA-12S1N8A8008 - 1619645



Cable connector, straight, Shielded, Screw locking, M23, Number of positions: 12, Type of contact: Socket, Crimp connection, Cable diameter: 10 mm...14.5 mm

---

#### Device marking

## Sensor/actuator box - SACB-6/ 6-L-M23 180 - 1692695

### Accessories

Zack marker strip - ZBN 18:UNBEDRUCKT - 2809128



Zack marker strip, Strip, white, Unlabeled, Can be labeled with: Plotter, Mounting type: Snap into tall marker groove, For terminal block width: 18 mm, Lettering field: 18 x 5 mm

---

### Master cable, assembled

Female connector - RCK-TGUM/BL12/ 5,0PUR-U - 1684014



M23 socket, straight, 12-pos., with 5 m master cable, pin 9 and 10 bridged

---

Female connector - RCK-TGUM/BL12/10,0PUR-U - 1684027



M23 socket, straight, 12-pos., with 10 m master cable, pin 9 and 10 bridged

---

Female connector - RCK-TWUM/BL12/ 5,0PUR-U - 1684030



M23 socket, angled, 12-pos., with 5 m master cable, pin 9 and 10 bridged

---

Female connector - RCK-TWUM/BL12/10,0PUR-U - 1684043



M23 socket, angled, 12-pos., with 10 m master cable, pin 9 and 10 bridged

## Sensor/actuator box - SACB-6/ 6-L-M23 180 - 1692695

### Accessories

Female connector - V-RC/TGUM 11/KVD 11/LBL 12 - 1000041



M23 socket, 12-pos., straight, freely configurable, with solder connection, for external cable diameter of 8 mm ... 12 mm

---

Female connector - V-RC/TWUM 11/KVD 11/LBL 12 - 1000043



M23 socket, 12-pos., angled, freely configurable, with solder connection, for external cable diameter of 8 mm ... 12 mm

---

### Protective cap

Protective cap - MSK 1 - 1665897



M23 metal sealing cap, for unoccupied M23 connectors, without steel wire

---

Protective cap - MSK 2 - 1665907



M23 metal sealing cap, for unoccupied M23 connectors, with steel wire

---

Protective cap - KSK 1 - 1685013



Plastic sealing cap, for unoccupied M23 connectors

---

## Sensor/actuator box - SACB-6/ 6-L-M23 180 - 1692695

### Accessories

Screw plug - PROT-M12 - 1680539



An M12 screw plug for the unoccupied M12 sockets of the sensor/actuator cable, boxes and flush-type connectors

---

### Screwdriver tools

Tool - SAC BIT M12-D15 - 1208432



Nut for assembling sensor/actuator cables with M12 connector and for M12 connectors with QUICKON fast connection technology, for 4 mm hexagonal drive

---

Tool - SACC BIT M12-D20 - 1208445



Nut for assembling SACC M12 connectors for free assembly, excluding M12 connectors with QUICKON fast connection technology, for 4 mm hexagonal drive

---

### T-distributor

Housing - RC-T 12/1BU2ST - 1685107



M23 T-distributor, 12-pos., with one M23 socket and two M23 plugs; position 9 and 10 bridged

---

### Torque tool

Torque screwdriver - TSD 04 SAC - 1208429




Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors

---

### Drawings


# Sensor/actuator box - SACB-6/ 6-L-M23 180 - 1692695

Schematic diagram




M12 slot, socket, 4-pos.

Schematic diagram



M23 plug connection pin, 12-pos.

Circuit diagram



Dimensioned drawing

