

Features

- 1in BSPP
- Single check valve
- Low pressure drop
- Brass body
- Nylon stem
- Domestic & industrial
- ISO 228 parallel threads

RS PRO 1in BSPP Single Non-Return Valve

RS Stock No.: 486-164



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A single check (1 ball) non-return valve intended to prevent the flow of gasses or fluids in the wrong direction within pipe networks. Suitable for use in domestic and industrial environments in hydraulic and pneumatic systems.

General Specifications

Type	Single
Body Material	Brass
Stem Material	Nylon
Seals	NBR 65 SH/PS
Thread Size	1in
Thread Standard	BSPP
Thread Type	Parallel (ISO 228)

Mechanical Specifications

Height	60.5mm
Width	47.5

Operation Environment Specifications

Working Temperature Range	-20 to 100°C
Maximum Working Pressure	12bar