

Datasheet

RS Pro D-sub Interface Module, DIN Rail Mount, Male, 37 Pole, 125 V ac/dc, 1.5A, 107mm

RS Stock No: **665-9706**



Product Details

RS Pro D-sub interface module has a male plug with 37 contacts to supports 14 to 22 AWG D-sub miniature connection into screw clamp terminals. This module features a compact 47 mm profile with simple assembly. It has 1.5 A of current rating per pin. The module has an insulating stripping length and screw/tension spring of 6 to 7 mm. It is the best alternative to pure individual wire approach. It measures 47 x 107 mm.

Features and Benefits

- Interconnect D-Subminiature into screw-clamp terminals
- D-Sub according to MIL-C-24308/DIN41652
- Compact 47 mm profile
- Rail mount on DIN-rail TS35
- 1.5 A current rating per pin
- Stripping length, screw/tension spring of 6 to 7 mm
- Alternative to pure individual wire approach

**Specifications:**

Cable CSA	0.2 to 2.5 mm ²
Connector Type	D-Sub
Current Rating	1.5 A
Depth	47 mm
Dimensions	107 x 61 x 47 mm
Gender	Male
Length	107 mm
Maximum Operating Temperature	+50°C
Minimum Operating Temperature	-20°C
Mounting Type	DIN Rail Mount
Number of Contacts	37
Test Proof Voltage	0.6 kV
Voltage Rating	125 V ac/dc
Width	61 mm
Wire Size	22 to 14 AWG
Number of Poles	37