

# Rittal – The System.

Faster – better – everywhere.

## ► Metal gland plate with metric knockouts – SZ 1581.200

Date : Apr 25, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# Metal gland plate with metric knockouts – SZ 1581.200

created: 25.04.2020 on [www.rittal.com/com-en](http://www.rittal.com/com-en)



## Product description

<b>Description:</b>	Simply knock out the holes for the cable glands using a screwdriver.
<b>Material:</b>	Sheet steel
<b>Colour:</b>	RAL 7035
<b>Protection category IP to IEC 60 529:</b>	IP 55 if installed correctly
<b>Note:</b>	The allocation of gland plate sizes is indicated on the relevant enclosures

## Product features

<b>To fit:</b>	Enclosure type: KX
<b>Cable entry:</b>	Number x metric diameter: 12 x M20
<b>Packs of:</b>	1 pc(s).
<b>Copper weight (kg per piece):</b>	0
<b>EAN:</b>	4028177940536
<b>Customs tariff number:</b>	94039010
<b>ETIM 7.0:</b>	EC000211
<b>ETIM 6.0:</b>	EC000211

<b>eCl@ss 8.0/8.1:</b>	27142421
<b>eCl@ss 6.0/6.1:</b>	27189190
<b>Product description:</b>	KX Metal gland plate, with metric knockouts, for cable diameter M20
<b>Approvals</b>	
<b>Approvals:</b>	UL + C-UL
<b>Certificates:</b>	EAC