

### Main

Range compatibility	Altivar&nbsp;Process ATV900
Accessory / separate part type	Braking unit
Product or component type	Braking resistor
Ohmic value	6.7 Ohm

### Complementary

Product compatibility	Variable speed drive ModBuo 160 kW 380...480 V Variable speed drive ModBuo 315 kW 380...480 V Variable speed drive ModBuo 500 kW 380...480 V Variable speed drive ModBuo 630 kW 380...480 V Variable speed drive ModBuo 800 kW 380...480 V
Duty cycle	Severe cycle (heavy duty) <48 s braking with 150 % braking torque for a 120 s cycle Severe cycle (normal duty) <48 s braking with 120 % braking torque for a 120 s cycle Severe cycle (heavy duty) <60 s braking with 150 % braking torque for a 200 s cycle Severe cycle (normal duty) <60 s braking with 120 % braking torque for a 200 s cycle
Average power available	60 kW at 40 °C
Electrical connection	M10 terminal
Protection type	Thermal protection via drive
Width	1060 mm
Height	1285 mm
Depth	540 mm
Net weight	120 kg

### Environment

IP degree of protection	IP23
Ambient air temperature for storage	-25...70 °C
Ambient air temperature for operation	-25...40 °C