

Product Specification PDF

Date	Correct as of 12th Jun 2026
Brand	C.K Tools
Product	T3589
Description	C.K Digital Level
Barcode	5013969252521
Commodity code	9015309000
Country of origin	CN



Features & Benefits	~270mm aluminium inclinometer & spirit level - compact, precise and tough ~High accuracy: 0.1° at 0°, 45° & 90°; 0.2° at all other angles. ~Bright 55x15mm illuminated display with auto-rotate view ~Multiple readouts: Degrees, %, mm/m, in/ft - with hold & reference function ~Horizontal & vertical green spirit vials for quick checks and accurate to 0.5mm/M ~Magnetic milled base for secure hands-free use on steel surfaces ~Double rubberised end caps for superior drop & shock protection ~Powered by 2 x AAA batteries (not included)
Warranty	12 Months

Product Weights and Measures				
	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	-	20
Width mm	268.8	85	-	22
Depth mm	22.7	35	-	17.2
Height mm	50	357	-	63
Weight	249	255	-	7.94
Packaging Information	Card use	Box	-	5-ply corrugated
	Card gms	6	-	940
	Plastic use	-	-	-
	Plastic gms	0	0	-
	Metal use	-	-	-
	Metal gms	0	-	-
	Timber use	-	-	-
	Timber gms	-	-	-