

Ti20-RBP

Rechargeable NiMH Battery Pack

Safety Information

The Ti20-RBP is a field-swappable, rechargeable Nickel Metal Hydride, 7.2 V, 1900 mAh battery.



A **Warning** identifies conditions and procedures that are dangerous to the user. A **Caution** identifies conditions and procedures that can cause damage to the Product or the equipment under test.

Warning

To avoid injury:

- Use the battery pack only as specified in the Fluke product-specific manual.
- Use only with compatible Fluke products
- Do not disassemble or short circuit the battery pack.
- Do not store the battery pack at temperatures >45 °C (113 °F) or operate for short durations >50 °C (122 °F).
- Do not incinerate or mutilate the battery pack.
- Must be recycled or disposed of properly
- Use only ac adapters approved by Fluke for the product to charge the battery or power the product.

Symbols

Symbol	Description
	Important information. See manual.
	This product complies with the WEEE Directive (2002/96/EC) marking requirements. The affixed label indicates that you must not discard this electrical/electronic product in domestic household waste. Product Category: With reference to the equipment types in the WEEE Directive Annex I, this product is classed as category 9 "Monitoring and Control Instrumentation" product. Do not dispose of this product as unsorted municipal waste. Go to Fluke's website for recycling information.

PN 4354709

May 2013

© 2013 Fluke Corporation. All rights reserved. All product names are trademarks of their respective companies. Specifications are subject to change without notice.

Specifications

Battery Type	NiMH, 7.2 V, 1900 mAh, 13.7 Whr
Dimensions	11 cm x 3 cm x 3 cm (4.3 in x 1.2 in x 1.2 in)
Operating Temperature	-10 °C to 50 °C (14 °F to 122 °F)
Long Term Storage Temperature	-20 °C to 45 °C (-4 °F to 113 °F)

How to Contact Fluke

To contact Fluke, call one of the following telephone numbers:

- USA: 1-800-760-4523
- Canada: 1-800-36-FLUKE (1-800-363-5853)
- Europe: +31 402-675-200
- Japan: +81-3-6714-3114
- Singapore: +65-6799-5566
- Anywhere in the world: +1-425-446-5500

Or, visit Fluke's website at www.fluke.com.

To register your product, visit <http://register.fluke.com>.

To view, print, or download the latest manual supplement, visit <http://us.fluke.com/usen/support/manuals>.