

# swivel flange SUA-50

Part number: 157324

FESTO

For cylinders ADVU, AEVU; matching clevis foot mountings LBN or LN, LSN.



## Data sheet

Feature	Value
Size	50
Assembly position	Any
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Ambient temperature	-40 ... 90 °C
Product weight	288 g
Materials note	Free of copper and PTFE Conforms to RoHS
Material mounting	Wrought Aluminium alloy
Material mounting pin	steel, galvanized
Material sleeve	Spring steel
Material bearing	Plastic
Material screws	Galvanised steel
Material lock	Spring steel
Material shaft	Steel With protective coating