


PRODUCT-DETAILS

OS25FF2210F

OS25FF2210F SWITCH FUSE



General Information

Extended Product Type	OS25FF2210F
Product ID	1SCA108637R1001
EAN	6417019418995
Catalog Description	OS25FF2210F SWITCH FUSE
Long Description	Switch Fuses,Front Operated,4-pole,22 (Between the Poles),NFC,10x38,Handle and shaft not included,Switched - Fusible Pole

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country of Origin	Lithuania (LT)

Popular Downloads

Data Sheet, Technical Information	1SCC311129D0201
Instructions and Manuals	1SCC311030M0202

Dimensions

Product Net Width	142 mm
-------------------	--------

Product Net Height	97 mm
Product Net Depth / Length	105 mm
Product Net Weight	0.8 kg

Technical

Rated Operational Current AC-21A (I_e)	(500 V) 25 A (690 V) 25 A
Rated Operational Current AC-22A (I_e)	(500 V) 25 A (690 V) 25 A
Rated Operational Current AC-23A (I_e)	(500 V) 25 A (690 V) 25 A
Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 5.5 kW (400 V) 11 kW (415 V) 11 kW (500 V) 15 kW (690 V) 22 kW
Conventional Free-air Thermal Current (I_{th})	q = 40 °C 25 A
Conventional Thermal Current (I_{the})	Fully Enclosed 25 A
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	1000 V
Rated Operational Voltage	500 V
Rated Short-time Withstand Current (I_{cw})	for 1 s 1 kiloampere rms
Rated Conditional Short-Circuit Current (I_{nc})	(690 V) 80 kA
Power Loss	at Rated Operating Conditions per Pole 3.5 W
Pollution Degree	3
Handle Type	Handle and shaft included
Fourth Pole Type	Switched - Fusible Pole
Switches Operating Mechanism	22 (Between the Poles)
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Fuse Size	10x38
Fuse System	NFC
Operating Mode	Front Operated
Standards	IEC 60947-3
Mounting Type	Base mounting
Number of Poles	4
Cable Cross-Section	0.75 ... 10 mm ²
Terminal Type	Screw Terminals
Tightening Torque	2 N·m
Fuse Type	NFC

Environmental

RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
-------------	--

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	1SCC311129D2702
--------------------------------	-----------------

DNV GL Certificate	1SCC311125D0203
EAC Certificate	EAC OT_OTDC_OTL_OTP_OTR_OTU_OTE_OETL_OESA_OESC_OTM_OS_OSM_p f
Instructions and Manuals	1SCC311030M0202
RoHS Information	1SCC311106D0203

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	240 mm
Package Level 1 Depth / Length	108 mm
Package Level 1 Height	130 mm
Package Level 1 Gross Weight	0.8 kg
Package Level 1 EAN	6417019418995

Classifications

Object Classification Code	Q
ETIM 4	EC001040 - Fuse switch disconnecter
ETIM 5	EC001040 - Fuse switch disconnecter
ETIM 6	EC001040 - Fuse switch disconnecter
ETIM 7	EC001040 - Fuse switch disconnecter
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Switches → Switch Fuses

