

DIN rail mounting hour - CHMDR CHMDR Part number 99793712



- Width equivalent to 2 modules
- Capacity 100,000 hrs (99,999.99 hrs)
- Extended temperature range: -10 →+70°C (AC version)
- DIN rail mounted according to EN 50022
- IP65 on panel
- Highly resistant to shocks and impacts
- Colour: RAL 7035 grey
- Screw terminals

	Type	Operating frequency (Hz)	Voltages
99793710	CHMDR	50	24 VAC
99793712	CHMDR	50	115 VAC
99793714	CHMDR	50	230 VAC
99793810	CHMDR	DC	10 →27 VDC

General characteristics

Counting capacity	99,999.99
Reset to zero	Not included
Read accuracy	1/100 h
Height digits (mm)	3,5
Colour of hour numbers	White on a black background
Colour of decimal digits	Black on a white background
Accuracy	VAC/VDC: < 0.01% (24 hrs)
Counting input mode	Addition
Degree of protection front face	IP 65
Tolerance	VAC± 10%
Temperature limits use (°C)	VAC: -10 →+70 VDC: -10 →+50
Temperature limits stored (°C)	-40 →+80
Certifications	CE
Connection	Screw terminals
Consumption	VAC: approx. 2.5 VA VDC: approx. 1 W
Vibration resistance	1G (10-500 Hz)
Test voltage for AC models	2 000 VAC 50 Hz
Weight (g)	60

Dimension Diagram : CHMDR

