



Body protection

DOONHV Fluorescent yellow

OUTDOOR HIGH VISIBILITY

Down jacket combining resistance and soft warmth with its 100% recycled fill, for day and night visibility



Specific benefits



Comfort

- Lightweight clothing for greater comfort



Durability

- Certified EN ISO 20471 after 50 washes
- 100% recycled wadding for a more environmentally-friendly product
- Ripstop fabric to prevent tearing

Technologies & labels



RIPSTOP

RIPSTOP



GRS

Certifications and norms



EN ISO 20471

CLASS 3
X25



CATEGORY 2

EN ISO 13688

Applications

- Public works
- Building
- Public services

Protects against risks



Cold



High vis



Body protection

DOONHV Fluorescent yellow

OUTDOOR HIGH VISIBILITY

Down jacket combining resistance and soft warmth with its 100% recycled fill, for day and night visibility

Standards - Details

Technical details

Type of workwear	High-visibility water-repellent down jacket
Gender	Mixte
Size range	S → 3XL
Workwear color	Yellow
Support material details	Canvas Ripstop 100% Polyester PU coating 2 rolled layers
Lining material	Taffeta 100% polyester
Lining material	100% recycled polyester fibre filling
Hood type	Fixed hood
Fastening	Zipper fastening
Lower sleeve	Bias
Lower body	Bias
Top Reflective piping	Chest and sleeves (4 bands)
Number of exterior pockets (Only)	2
External pockets	2 zipped pockets
Marking type	Screen printing, Transfer printing
Reflective piping	Reflective piping place
Technologies and labels	RIPSTOP, GRS



Protective clothing

DOONHV

OUTDOOR HIGH VISIBILITY

Down jacket combining resistance and soft warmth with its 100% recycled fill, for day and night visibility

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
DOOHVORPT	Fluorescent orange	S	DOONHV	3295249234058	13295249234055	10	1	8.5 kg	40.4 cm	60.4 cm	37.4 cm
DOOHVORTM	Fluorescent orange	M	DOONHV	3295249234270	13295249234277	10	1	8.8 kg	41.0 cm	60.4 cm	40.0 cm
DOOHVORGT	Fluorescent orange	L	DOONHV	3295249234287	13295249234284	10	1	9.0 kg	41.4 cm	60.2 cm	37.4 cm
DOOHVORXG	Fluorescent orange	XL	DOONHV	3295249234294	13295249234291	10	1	9.3 kg	40.8 cm	61.2 cm	38.6 cm
DOOHVORXX	Fluorescent orange	XXL	DOONHV	3295249234300	13295249234307	10	1	9.6 kg	40.8 cm	61.6 cm	38.4 cm
DOOHVOR3X	Fluorescent orange	3XL	DOONHV	3295249234317	13295249234314	10	1	10.0 kg	40.4 cm	62.8 cm	38.2 cm
DOOHVJAPT	Fluorescent yellow	S	DOONHV	3295249234041	13295249234048	10	1	8.4 kg	40.6 cm	59.8 cm	37.2 cm
DOOHVJATM	Fluorescent yellow	M	DOONHV	3295249234225	13295249234222	10	1	8.6 kg	41.0 cm	60.0 cm	38.2 cm
DOOHVJAGT	Fluorescent yellow	L	DOONHV	3295249234232	13295249234239	10	1	9.0 kg	41.0 cm	61.4 cm	38.6 cm
DOOHVJAXG	Fluorescent yellow	XL	DOONHV	3295249234249	13295249234246	10	1	8.0 kg	62.0 cm	44.0 cm	27.0 cm
DOOHVJAXX	Fluorescent yellow	XXL	DOONHV	3295249234256	13295249234253	10	1	9.7 kg	41.8 cm	61.0 cm	38.8 cm
DOOHVJA3X	Fluorescent yellow	3XL	DOONHV	3295249234263	13295249234260	10	1	8.0 kg	62.0 cm	44.0 cm	27.0 cm



Multiple sales



Minimum sales



Box Width



Box Depth



Box Height