

## *// RUN-R //*



**100 %  
metal  
free**



### **RUN-R 100 LOW**

Art. Nr.: 62583

EN ISO 20345: 2011 - S1P SRC

Sizes: 37 - 48

### *APPLICATIONS //*

metal free model for trades men, light industry, warehousing and logistics, manufacturing, dry environments

### *TECHNICAL SPECIFICATIONS //*

**sole:** PU2D | very lightweight | highly flexible | excellent shock absorption | excellent levels of grip (SRC) | oil, hydrocarbon & chemical-resistant | grooves at the back of the heel for a better grip when the heel first touches the ground & deep grooves for better grip in the forefoot area | pronounced heel & GRIPSTEP profile for ladders and stairs

**upper:** mesh and TPU support structure for excellent abrasion resistance

**lining:** 3D polyester mesh for excellent breathability, quick drying

**toe cap:** metal free

**penetration-resistant midsole:** metal free

**hygienic insole:** removable | anatomically shaped with shock absorbers in the heel & forefoot | microfibre top layer for better abrasion resistance & durability | very high moisture absorption capacity & fast drying bottom layer made from 90% recycled PU foam | washable at 30°C enhances hygiene

**easy lock system:** extra standard laces supplied in the box

**weight:** 550 g in size 42