

High-dexterity light-duty work gloves, offering superb grip and light chemical resistance

- **Certified ergonomics:** With certification from United States Ergonomics, AlphaTec® 58-128 chemical-resistant gloves feature a fitted shape, reduce hand fatigue and are proven to support musculoskeletal health during repetitive tasks
- **Assured protection:** These industrial gloves' thin nitrile coating provides an effective barrier against oils and irritant fluids, for reliable personal protection suitable for light-duty applications
- **Enhanced grip:** AlphaTec® 58-128 protective gloves also boast an ANSELL GRIP™ Technology coating polymer, which enhances grip when handling wet or oily parts
- **Improved comfort:** As its ergonomic shape conforms to the natural contours of the wearer's hand, it is easy to wear and use

Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical

Applications

- Body painting including surface inspection
- Applying sealers, touching up
- Press injection molding
- Equipment repair & maintenance
- Assembling and mounting components
- Painting or cleaning tools or robots
- Final assembly
- Metalwork, glass processing
- Assembly & inspection of components
- Warehousing of raw materials
- Testing



Key Features

- **Ergonomic certification:** A fitted shape, for good musculoskeletal health
- **Thin nitrile coating:** Protection against oils and irritant fluids
- **ANSELL GRIP™ Technology coating:** Easier handling of wet or oily parts

Vulcanization Chemical Accelerators

- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Technologies



ANSELL GRIP™

Ansell Grip Technology



ERGOFORM™

Ergonomic Design Technology



Performance Standards



0493



2121A



JKLOPT



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGT H	COLOR	PACKAGE
AlphaTec® 58-128	Liner Material: Nylon Coating Material: Nitrile Featured Technology: ANSELL GRIP™	7, 8, 9, 10, 11	280 / 11	Grey	• 12 pairs/polybag; 12 polybags/carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.