

FEATURES

- Material 304 / 1.4301 stainless steel
- IP66 rating
- Lids with black neoprene gasket and 4 x M6 captive hexagon headed screws
- Operating temperature -20 °C to +110 °C
- Multiple DIN rail fixing points, M5
- External M6 earth stud

RS PRO Junction Boxes

RS Stock No.: 749-1857



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO IP66 Sealed Terminal Boxes

Introducing a range of RS PRO heavy duty terminal boxes. These boxes are designed for housing DIN rail terminals and accessories. Constructed from 1.2 mm AISI 304 natural finish stainless steel and fitted with a black neoprene gasket these enclosures provide an IP66 rating.

General Specifications

Body Material	Stainless Steel
Base Material	Stainless Steel
Gasket Material	Neoprene
Application	Power Management
Colour	Unpainted
Lid Colour	Unpainted
Temperature Range	-20 °C to +110 °C
Shape	Rectangular
Surface Finishing	Untreated
Mounting Type	Wall
Wall Thickness	1.2mm
Size	Small
Cover Locking	Screw

Mechanical Specifications

Length	150mm
Width	80mm
Height	150mm
Dimensions	150 x 80 x 150mm

Protection Category

IP Rating	IP66
------------------	-------------

Approvals

Declarations	RoHS Certificate of Compliance
---------------------	---------------------------------------

Similar Products

Stock No.	Brand	Product Name	Material	Dimensions	Number of ways
122-030	RS PRO	Junction Box	Steel	300 x 200 x 120mm	
144-4457	RS PRO	Junction Box	GRP	220 x 120 x 90mm	