

FEATURES

- Versatile and easy to fit
- Hexagonal design allows tightening with a wrench
- Lock PCB securely into place
- Mild steel material for mechanical strength and resistance to hightemperature environments
- Zinc plating for resistance to oxidation and corrosion

RS PRO Steel Hex Standoff Male/Female, 20mm, M4 x M4

RS Stock No.: 806-6575



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS Pro a range of robust, high-quality hexagonal shaped standoffs made from zinc plated mild steel with a metric internal thread or threaded stud on either end. These versatile standoffs are designed to securely mount your PCB as well as elevating it from other components such as the inside of a computer chassis or another PCB. They are also ideal for improving airflow space around components when the equipment becomes hot. These stand-offs are available in a range of different heights and threads sizes to suit a wide range of PCB applications.

General Specifications

Gender Type	Male/Female
Material	Steel
Body Shape	Hex
Finish	Zinc Plated
Plating	Zinc
Application	Consumer electronics, office machinery, Datacom's and telecommunications equipment.


Mechanical Specifications

Body Length	20mm
Thread Size	M4 x M4
Stud Length	8mm
Thread Size A	M4
Thread Size B	M4
Hex Size Across Flat	7mm
Hole Depth	15mm
Internal Thread Size	8mm

Approvals

Compliance/Certifications	EN61340





RS Article	Description	Material	Plating	Н	D	P1	P2	P3	L	
8066714	Brass Hex Threaded Spacer M4x10mm M/F	Brass	s Nickel	7			7	8.5	10	
8066718	Brass Hex Threaded Spacer M4x12mm M/F						8	10	12	
8066727	Brass Hex Threaded Spacer M4x15mm M/F						10	13	15	
8066720	Brass Hex Threaded Spacer M4x20mm M/F						10	15	20	
8066724	Brass Hex Threaded Spacer M4x25mm M/F				M4	8	10	15	25	
8066733	Brass Hex Threaded Spacer M4x30mm M/F	Didoo			IVI-	0	10	15	30	
8066736	Brass Hex Threaded Spacer M4x35mm M/F						10	15	35	
8066730	Brass Hex Threaded Spacer M4x40mm M/F						10	15	40	
8066749	Brass Hex Threaded Spacer M4x45mm M/F						10	15	45	
8066742	Brass Hex Threaded Spacer M4x50mm M/F						10	15	50	
8066632	Brass Hex. Threaded Spacer M5x10mm						7	8.5	10	
8066635	Brass Hex. Threaded Spacer M5x15mm			8			10	13	15	
8066639	Brass Hex. Threaded Spacer M5x20mm		Brass Nickel				10	15	20	
8066648	Brass Hex. Threaded Spacer M5x25mm						10	15	25	
8066641	Brass Hex. Threaded Spacer M5x30mm	Brass			M5	8	10	15	30	
8066645	Brass Hex. Threaded Spacer M5x35mm				CIVI	0	10	15	35	
8066654	Brass Hex. Threaded Spacer M5x40mm						10	15	40	
8066657	Brass Hex. Threaded Spacer M5x45mm						10	15	45	
8066651	Brass Hex. Threaded Spacer M5x50mm							10	15	50
8066660	Brass Hex. Threaded Spacer M5x60mm						10	15	60	

Standoffs



RS Article	Description	Material	Plating	Н	D	P1	P2	P3	L
8066663	Steel Hex. Threaded Spacer M6x15mm						10	12	15
8066667	Steel Hex. Threaded Spacer M6x20mm						10	12	20
8066676	Steel Hex. Threaded Spacer M6x25mm						10	15	25
8066679	Steel Hex. Threaded Spacer M6x30mm		Nickel			10	10	15	30
8066673	Steel Hex. Threaded Spacer M6x35mm	Steel		10	M6		10	15	35
8066682	Steel Hex. Threaded Spacer M6x40mm						10	15	40
8066685	Steel Hex. Threaded Spacer M6x45mm						10	15	45
8066689	Steel Hex. Threaded Spacer M6x50mm						10	15	50
8066698	Steel Hex. Threaded Spacer M6x55mm						10	15	55
8066691	Steel Hex. Threaded Spacer M6x60mm	1					10	15	60
8066607	Threaded spacer, mild steel,M3x5mm,M/F						3	4.3	5
8066588	Threaded spacer, mild steel,M3x10mm,M/F					8	6	8.5	10
8066572	Threaded spacer, mild steel,M3x15mm,M/F	Steel Zinc	5	M3		8	13	15	
8066613	Threaded spacer, mild steel,M3x20mm,M/F		,	INIO		8	15	20	
8066629	Threaded spacer, mild steel,M3x25mm,M/F					10	10	15	25
8066617	Threaded spacer, mild steel,M3x30mm,M/F					10	10	15	30
8066578	Threaded spacer, mild steel,M4x10mm,M/F						6	8.5	10
8066562	Threaded spacer, mild steel,M4x15mm,M/F			7	M4	8	8	13	15
8066575	Threaded spacer, mild steel,M4x20mm,M/F	Steel	Zinc				8	15	20
8066604	Threaded spacer, mild steel,M4x25mm,M/F					10	10	15	25
8066590	Threaded spacer, mild steel,M4x30mm,M/F					10	10	15	30

RS Article	Description	Material	Plating	Н	D	Hole	L	
8066695	Brass Hex Threaded Spacer M4x30mm Female	Brass	Brass Nickel		M4	10	10	30
8066705	Brass Hex Threaded Spacer M4x35mm Female					10	10	35
8066708	Brass Hex Threaded Spacer M4x40mm Female			7		10	10	40
8066702	Brass Hex Threaded Spacer M4x45mm Female					10	10	45
8066711	Brass Hex Threaded Spacer M4x50mm Female					10	10	50
8066601	Threaded spacer, mild steel,M3x5mm,F/F	Steel	Zinc		МЗ		5	
8066597	Threaded spacer, mild steel,M3x10mm,F/F					10		10
8066584	Threaded spacer, mild steel,M3x15mm,F/F			5		10	10	15
8066581	Threaded spacer, mild steel,M3x20mm,F/F			5		10	10	20
8066623	Threaded spacer, mild steel,M3x25mm,F/F					10	10	25
8066610	Threaded spacer, mild steel,M3x30mm,F/F					10	10	30
8066566	Threaded spacer, mild steel,M4x10mm,F/F	Steel				1	10	
8066550	Threaded spacer, mild steel,M4x15mm,F/F					10	10	15
8066569	Threaded spacer, mild steel,M4x20mm,F/F		Zinc	7	M4	10	10	20
8066594	Threaded spacer, mild steel,M4x25mm,F/F					10	10	25
8066626	Threaded spacer, mild steel,M4x30mm,F/F					10	10	30