

Actuator

45-
2P01.1E10.000

Distribution by
Rs-online



<https://rs-online.eao.com/p/45-2P01.1E10.000>

Your product:



45-2P01.1E10.000 Actuator

FRONT

Front dimension:	Ø 30 mm
Front form:	Round
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Design:	Raised
Mounting cut-out:	Ø 22.3 mm
Mounting type:	Panel mounting

ELECTRICAL CHARACTERISTICS

Operating voltage:	300 V DC
Insulation voltage:	Rated value 500 V
Power (W):	0.5
Switching rating:	
Resistance:	100 kΩ

MECHANICAL CHARATERISTIC

Terminal:	Screw terminal
Mechanical lifetime:	25 000 turning cycles
Tightening torque:	0.8 ... 1 Nm fixing nut
Operating frequency:	1 800/h
Terminal details 1:	– With end sleeves 2 x (0.5 ... 0.75 mm ²)

Solid

Terminal details 2:

Finely stranded
– With end sleeves 2 x (0.5 ... 1.5 mm²)
– Without end sleeves 2 x (0.5 ... 0.75 mm²)
– For AWG cables for auxiliary contacts 2 x (18 ... 14)

Weight:

0.06 kg

AMBIENT CONDITION

IP Protection:

IP20 Terminal, IP65, IP66, IP67 housing

Operating temperature:

– 25 °C ... + 70 °C

Storage temperature:

– 40 °C ... + 80 °C

Shock resistance:

According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms

Vibration resistance:

According to IEC 60068-2-6: 10 ... 500 Hz: 5 g

Climate resistance:

During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6

CERTIFICATE

REACH:

REACH compliant

RoHS:

RoHS compliant

OTHER


Short Description:

Actuator, Ø 22.3 mm, Ø 30 mm, Round, Black, Plastic, Screw terminal


Housing material:

Plastic


Wiring diagrams:



Component layouts:



Mounting cut-outs:



Dimension drawings:

