



PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 8:14 (UTC)



6208DDU

Single-Row Deep Groove Ball Bearings

Boundary Dimensions

d	40	mm	Bore diameter
D	80	mm	Outside diameter
B	18	mm	Width
r (min.)	1.1	mm	Chamfer dimension

Basic Load Ratings

Cr	32000	N	Basic dynamic load rating
C0r	17900	N	Basic static load rating

Speeds

Grease	5600	min-1	Grease lubrication
--------	------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	46.5	mm	Diameter of shaft abutment
da (max.)	50.5	mm	Diameter of shaft abutment
Da (max.)	73.5	mm	Diameter of housing abutment
ra (max.)	1	mm	Radius of shaft or housing fillet

Calculation factors

fo	14		Factor
----	----	--	--------

Additional information

z	9		Number of Balls
Dw	11.906	mm	Ball Diameter

Mass

Mass approx.	0.366	kg	Mass approx.
--------------	-------	----	--------------

