



FIX Adapter Germany CEE7/7 - Switzerland T12 3-pole black, pack of 100 pcs.



Item No.: 14 9563 1
EAN Code: 7611007056605

Description

FIX Adapter Germany CEE7/7 - Switzerland T12, 3-pole, input socket for: Schuko (CEE 7/7), output plug: Switzerland (Type 12), input voltage: max. 250V, power: max. 2500W, load: max. 10A, black, pack of 100 pcs.

Specifications

Type	Fixed Adapter
Brand	STEFFEN
Model	Schuko (CEE 7/7) - Type 12
Number of Sockets	1
Socket Type	Schuko (CEE 7/7)
Increased Touch Protection	No
Product Colour	Black
Rated Current	10 A
Rated Voltage	250 V
Rated Power	2500 W
Plug Type	Type 12
Main Material	Plastic
Halogen-Free	No
UV Resistance	No

Application	Indoor
K2 Suitable for Construction Sites	No
IP Rating	IP20
Operating Temperature Range	-5...+45 °C
Safety Features	Permanently Attached and Non-Removable
Additional Features	Practical Installation Aid Included
Product Height	45 mm
Product Width	45 mm
Product Depth	60 mm
Net Weight	0.05 Kg
Packaging	Open
