

Features

- Jaws move in parallel throughout use.
- Serrated jaws for improved grip.
- V-slot to feed and hold wire and rod securely along jaw length.
- Wire can be threaded down throat of plier.
- Multiplies hand force by 23x for less cutting effort.
- Precision-machined and hardened blades.
- Jaws and blades case hardened to HRC 57 for durability.

RS PRO Side Cutter Parallel Plier For Hard Wire 160 mm

RS Stock No.: 0441178



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Side Cutter Parallel Plier For Hard Wire

The combination plier reimagined, featuring a compound-lever-action cutter and parallel-action jaws. The complete multi-function plier. With serrated jaws for a greater grip.

Great for manipulating, straightening and cutting wire, with a v-slotted jaw and integrated cutter. Multiplies hand force by 23x for less cutting effort.

Engineered with serrated parallel jaws for a vice-like grip on square and hexagonal fastenings.

Benefits

- Multi-purpose tool, perfect for gripping, manipulating and cutting.
- Parallel jaws grip securely along their whole length.
- Hold square and hexagonal fastenings in a vice-like grip.
- Manipulate, straighten and remove kinks in wire.
- Cut both hard and soft wire with ease.
- Built to last, with a robust construction and rust-resistant finish.

Applications

A toolbox essential, with rugged construction and powerful lever action, ideal for:

- Design engineers.
- Maintenance Technicians.
- Trade Specialists.

General Specifications

Plier Type	Side Cutter Parallel Plier
Number of Pieces	1
Overall Length	167mm
Cutting Capacity	Piano wire 2 mm Ø, hard wire 2.5 mm Ø, soft wire 4.0 mm Ø
Material	Steel jaws, zinc-plated steel handles
ESD Safe	No
Jaw Length	34 mm useable jaw length
Jaw Opening	14 mm
Jaw Width	9 mm
Non Sparking	No
Height Safe	No

Approvals

Declarations	REACH DoC
--------------	-----------

Standards Met

BS 3087-7:1996, ISO 5747:1995

Similar Products

Stock No.	Brand	Product Name	Jaw Opening	Parallel	Overall Length
0606317	RS PRO	CENTRE CONDUCTOR CUTTING NIPPER	Up to 25 mm (Duct Rod Ø)	No	110 mm
0606320	RS PRO	Bullet & Snap Connector Insert Tool	46mm	No	145mm
0606319	RS PRO	Spanner Quick Grip	25 mm Max	No	135mm
0606316	RS PRO	Security Crimping and Cutter Plier	0.9mm (Ø cables)	No	212mm
0434623	RS PRO	Snipe Nose Serrated Jaws Parallel Plier	10mm	Yes	125mm
0606318	RS PRO	Snipe Nose Smooth Jaws Parallel Plier	10mm	Yes	125mm
0434621	RS PRO	Fine Nose Round Jaws Parallel Plier	11mm	Yes	125mm
0606312	RS PRO	Fine Clamping Plastic Jaws Parallel Plier	20mm	Yes	168mm
0434622	RS PRO	Flat Nose Nylon Jaws Parallel Plier	10mm	Yes	140mm
0441178	RS PRO	Side Cutter Parallel Plier for Hard Wire 125mm	10mm	Yes	125mm
0606314	RS PRO	Side Cutter Parallel Plier for Hard Wire 160mm	14mm	Yes	167mm
0606313	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm	8mm	Yes	140mm
0434617	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm, w/ Grip Handle	8mm	Yes	140mm

