

Jig Saw LXT®

DJV186

18V, 0 – 2 900 min⁻¹

Model DJV186 is a Jig Saw powered by an 18V LXT Li-Ion battery

Features and benefits: Stroke length 18 mm.
Variable speed control by trigger. 3 orbital settings +
Straight cutting



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Strokes per Minute (SPM)	0 - 2900 min ⁻¹
Length of Stroke	18 mm
Max. Cutting Capacity in Wood (90°)	65 mm
Max. Cutting Capacity in Steel (90°)	6 mm
Capacity Aluminium	10 mm
Orbital Action	✓
Tool weight with battery	1,9 - 2,2 kg
Product Dimensions (L x W x H):	257 x 81 x 196 mm
Max. Bevel Range (Left)	0 - 45 °
Product net weight	1,6 kg
Vibration Level, Cutting Boards	7,5 m/s ²
Vibration Uncertainty (K Factor), Cutting Boards	1,5 m/s ²
Vibration Level, Cutting Sheet Metal	4,2 m/s ²
Vibration Uncertainty (K Factor), Cutting Sheet Metal	1,5 m/s ²

User benefits

- Compact and lightweight design
- Variable speed control dial enables user to match the speed to the application for greater versatility
- 3 orbital settings
- Slim design with rubberised grip for comfort
- Tilting base for bevel cuts from 0° - 45°
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makitaauk.com



Related products

Other

User manual

Parts drawing