

Stainless Steel Cable Ties



Product Specification

Material: Stainless Steel (316 grade), available with black polyester/epoxy resin coating

Approval: DNV, Lloyd's, UL, ABS

Application: Marine, chemical, oil & gas, Maintenance

Temperature: Uncoated : - 80°C ~ + 539°C Coated : - 80°C ~ + 150°C

Type: Non-releasable, ladder cable ties

Dimensions:

| RS Article | Material | Colour | Width (mm) | Length (mm) | Min. Tensile Strength (Kg.) | Max Bundle Dia. (mm) |
|------------|-----------------|--------|------------|-------------|-----------------------------|----------------------|
| 121-618 | SS 316 | Silver | 7 | 225 | 46 | 70 |
| 121-624 | SS 316 | Silver | 7 | 300 | 46 | 95 |
| 121-630 | SS 316 | Silver | 7 | 610 | 46 | 190 |
| 121-646 | SS 316 | Silver | 12 | 610 | 114 | 190 |
| 121-652 | SS 316 (coated) | Black | 7 | 225 | 46 | 70 |
| 121-668 | SS 316 (coated) | Black | 7 | 300 | 46 | 95 |
| 121-674 | SS 316 (coated) | Black | 7 | 610 | 46 | 190 |