



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought



TE Part #829261-2
HD.FEMALE SCREWLOCK




TE Part #1393219-3
PE014005



TE Part #282857-2
TERMI-BLOK PCB MOUNT 90 2P.5



TE Part #1879378-7
TLR 2512 2.0W R0005 1% 50PPM 2K RL



TE Part #215297-3
3P HV100 REC CON. TE, 7.0MM



TE Part #1676250-2
RN 0805 20K 0.1% 10PPM 1KRL



TE Part #338068-6
MICRO-MATCH FTE, 6P



TE Part #1-1649329-3
RT424012



TE Part #1393845-5
RP821024



TE Part #4-1879131-1
RN 0402 8K06 0.1% 10PPM 1K RL

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_1623916-6_BA.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1623916-6_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1623916-6_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

SMD Trimmers - Type 3203 Series - Tyco Electronics Passives

English

