

Ganz Genstar NVR-Series



With up to 6MP recording are a number of different Ganz IP network recorder available. Starting with the 4-channel up to 32 channel recorder, suitable for numerous applications. Ideally matched to the recorder, incidentally, are the IP cameras from Ganz Genstar series.

- Up to 6 Megapixel recording
- Either 8, 16 or 32 channels
- Up to 25 frames / second
- H.264-Compression
- App for iOS & Android

Order data

Order number	Product description
NR8-4M71	H.264 4-Channel NVR, max. 6MP Recording, 4x RJ-45 (PoE), HDMI / VGA, 1x SATA-Interface, 2x USB, RJ-45, 255 x 47.5 x 235, 930g
NR8-8M71	H.264 8-Channel NVR, max. 6MP Recording, 8x RJ-45 (PoE), HDMI / VGA, 1x SATA-Interface, 2x USB, RJ-45, 372 x 44.5 x 311, 2.8kg
NR8-16M74	H.264 16-Channel NVR, max. 6MP Recording, 16x RJ-45 (PoE), HDMI / VGA, 4x SATA-Interface, 3x USB, RJ-45, 440 x 67 x 376, 3.6kg
NR8-32M78-0	H.264 32-Channel NVR, max. 6MP Recording, 2x RJ-45, HDMI / VGA, 8x SATA-Interface, 2x USB, RJ-45, 440 x 89.9 x 435, 7.2kg

Ganz Genstar NVR-Series



Technical specifications	NR8-4M71	NR8-8M71	NR8-16M74	NR8-32M78-0
Video standard	6MP/5MP/4MP/3MP/1080P/720P/D1			
Compression format	H.264			
Video input	4 x RJ-45 (PoE)	8 x RJ-45 (PoE)	16 x RJ-45 (PoE)	2 x RJ-45 (non-PoE)
Channels	4	8	16	32
Monitor output	1x HDMI / VGA (simultaneously)			
Audio input	-	1	1	1
Audio output	-	1	1	1
Alarm input	-	-	2	1
Alarm output	-	-	2	1
Hard disk quantity	1 (optional) max. 4TB per HDD	1 (optional) max. 4TB per HDD	4 (optional) max. 4TB per HDD	8 (optional) max. 4TB per HDD
Operating system	LINUX			
Recording format	6MP/5MP/4MP/3MP/1080P/720P/D1			
Recording mode	Continuous / Motion / Alarm			
Recording speed	6MP/5MP/4MP/3MP@15fps; 1080P@25fps			
Recording rate	4Ch Maximum 18Mbps	8Ch Maximum 36Mbps	16Ch Maximum 72Mbps	32Ch Maximum 144Mbps
Events	Motion / Video loss / External Alarm			
Movement sensor	@Camera			
Interfaces	2x USB, RJ-45	2x USB, RJ-45	3x USB, 2x RJ-45	2x USB, 2x RJ-45
Time/date settings	GMT Timezone, Auto DST, NTP			
Remote access	Firefox, Chrome, Safari, IE, iPhone, iPad, Android			
Data export	USB, HDD			
Protocols	RTP/RTCP, TCP/UDP, HTTP, DHCP, DNS, NTP			
Access authorisation	Password protection			
Operating environment	0° - 45°C	-10° - 45°C	-10° - 45°C	-10° - 45°C
Operating voltage	48VDC	110/220VAC	110/220VAC	110/220VAC
Dimensions (W × H × D) mm	255 x 47.5 x 235	372 x 44.5 x 311	440 x 67 x 376	440 x 89.9 x 435
Weight	930g	2.8kg	4.0kg	7.2kg